Trademark Trial and Appeal Board Electronic Filing System. <u>https://estta.uspto.gov</u>

ESTTA Tracking number: ESTTA1149471 Filing date:

07/27/2021

IN THE UNITED STATES PATENT AND TRADEMARK OFFICE BEFORE THE TRADEMARK TRIAL AND APPEAL BOARD

Proceeding	92070823
Party	Defendant Ikonix USA LLC
Correspondence Address	THOMAS J MOORE BACON & THOMAS PLLC 201 N. UNION ST., STE. 430 ALEXANDRIA, VA 22314-2649 UNITED STATES Primary Email: mail@baconthomas.com Secondary Email(s): tjmoore@baconthomas.com, jmiller@baconthomas.com 703-683-0500
Submission	Other Motions/Submissions
Filer's Name	Thomas J. Moore
Filer's email	mail@baconthomas.com, tjmoore@baconthomas.com
Signature	/Thomas J. Moore/
Date	07/27/2021
Attachments	2021-07-27 Declaration of Braverman cert serv signed.pdf(2049920 bytes) 2021-07-27 Exhibit A to Declaration of Braverman pp. 1-10.pdf(5732137 bytes) 2021-07-27 Exhibit A to Declaration of Braverman pp. 11-20.pdf(3804173 bytes) 2021-07-27 Exhibit A to Declaration of Braverman pp. 21-34.pdf(3419066 bytes)

IN THE UNITED STATES PATENT AND TRADEMARK OFFICE BEFORE THE TRADEMARK TRIAL AND APPEAL BOARD

ICware Systems, Inc. dba BatchTest Corporation, and BatchTest Corporation,

Petitioner,

٧.

Ikonix USA, LLC,

Respondent

Cancellation No. 92070823

DECLARATION OF BRAVERMAN

The undersigned, being hereby warned that willful false statements and the like are punishable by fine or imprisonment, or both, under 18 U.S.C. §1001, and may jeopardize the validity of the application or any registration resulting therefrom, declares that: all statements made herein of my own knowledge are true, and all statements made on information and belief are believed to be true.

The trademark BatchTEST has been used in commerce by Ikonix USA, LLC, as shown on pages 18 and 28 of the catalog submitted herewith (AR Catalog - Low Res.pdf) as Exhibit A.

The trademark BatchTEST has been used in commerce by lkonix USA, LLC, as shown on the display screen of the Software Options as shown below:

DECLARATION OF BRAVERMAN Cancellation No. 92070823 Page 2

L-APPS-01.ko	ni	Barcode/Model Selection Settin	195	
Maide Folk (Main) Data La	gging Deactivate	Nodel Number 💌	Gastal Number	
		Cutton Delenter 🔍	J~	
Drop-Down Martus	Discriptive Pop-Ups	Auto-Print	Paper Site	
Disstrument Autoscan			Select Printer	
0				
	L-APPS-01.lko Mode Demo Pallers % 50 Drop-Down Manus LLCT Auto-FB LST Auto-FB () Instrument Autoscan	L-APPS-03. lioni Mode Data Lopging Deactivets Demo Patters % 50 Lisbel Discriptive Pop-Ope Drop-Down Martus Discriptive Pop-Ope LCT Auto-FB MetchTEST Isstruement Autoscan Security	L-APPS-03. lkoni Mode Mode Data Lopging Desctivate Demo Ratium % Demo Rati	L-APPS-01.lkoni Mode Mode Mode Data Logging

July 27, 2021

1

Respectfully signed,

Adam Braverman Vice President Ikonix USA, LLC

DECLARATION OF BRAVERMAN Cancellation No. 92070823 Page 3

CERTIFICATE OF SERVICE

The undersigned hereby certifies that a copy of this document is being served on Petitioner by emailing it on the undersigned date addressed to the correspondence address of record in the TTABVUE database at the website of the U.S. Patent and Trademark Office as follows:

> Dinesh Patel BatchTest Corporation 2118 Walsh Ave, Suite 150 Santa Clara, CA 95050 BatchTest_TM@batchtest.com btcroot@gmail.com

July 27, 2021

/Thomas J. Moore/

TIM/IP/ICWA7001/Drafts

Exhibit A to the Declaration of Braverman July 27, 2021 U.S. Cancellation No. 92070823



Instruments for Electrical Safety Compliance Testing



Safety Is Our Only Focus®

Hipot • Ground Bond • Insulation Resistance • Leakage Current • Functional Run Medical Test Systems • HV/HC Multiplexers • Software Solutions

CUSTOMER HAPPINESS PROMISE

We aim to provide an amazing experience and quality testers that last a long time. If you're not satisfied with your tester, return it within 45 days for a full refund. Calibrate annually with us, or one of our authorized partners, and we'll extend your warranty an additional year for the service life of your tester, and at least five years after discontinuation. If it breaks during that time, we promise to fix it for free (unless abuse or excessive damage is present). When your tester reaches the end of its service life, we'll responsibly recycle it and give you a discount on a replacement.

*Annual calibration and inspection must be made in each successive year starting one year after the original purchase date in order to remain eligible for extended warranty coverage beyond the standard warranty period (five years).

5 YEAR WARRANTY

Your new tester is warranted to be free from defects in workmanship and material for a period of (5) years from date of shipment.

**5 year warranty is valid on any model purchased in 2021 or after.

ONGOING SUPPORT

We work to provide the best service and support in the industry. With decades of industry experience we are the pros you can trust to help you be compliant to NRTL standards. We'll work closely with you to help you achieve your goals. We've built a worldwide network of knowledgable partners, so you're covered no matter where you are.

OUR MISSION

We build relationships with manufacturers around the globe who trust our products and expertise in electrical safety compliance testing to protect their employees and customers from the dangers of electricity.







A HISTORY OF INNOVATION

1936 • 1939 •	Associated Research was founded. We introduced the first battery operated Megohmmeter, the Vibrotest, in the United States.	2001 •	We released our patented safety feature, SmartGFI®, to provide our customers with maximum operator protection during high voltage testing.
1966 💿	We commenced the first Cable Testing/Fault Location school known as ARU. ARU continued for over 25 years.	2012 (•	We launched the first electrical safety compliance analyzer with a built-in AC power source.
1993 •	We introduced the first complete family of microprocessor-controlled electrical safety instruments.	2013 (•	We developed the first mobile app in the electrical safety testing industry.
1995 •	We developed the first multi-function electrical safety compliance analyzer.	2017 •	We launched the Applications Consulting program.
1997 •	We released the first electrical safety instrument with a built-in multiplexer for multi-point testing.	2020 🧄	We Introduced Withstand, a Software as a Service (SaaS) platform, that is a cloud storage of your tests and data in one platform.
1999 🌢	We introduced Autoware, the first software package for automated instrument control, in the EST industry.		

FOCUSED ON EDUCATION

With over 80 years of industry experience, we have the resources and expertise to assist you with your educational needs throughout the life of your product.

- Quick Start Videos
- On-Site Training
- Quick Start Guides
- White Papers & Articles

SERVING THE COMMUNITY



We donate a portion of our profits to raising awareness about the dangers of electricity.

PRODUCT REFERENCE CHART



AC Hipot





DC Hipot



Ground Bond



Ground



Insulation



Leakage



Functional



Continuity Resistance Current Run AC Power Hypot[®] 3805 • • 3865 • ٠ • 3870 • • ٠ • HypotULTRA[®] 7800 500 VA • • • 7804 • • • • • 7820 • • 7850 ٠ • • • 7854 500 VA ٠ • • ٠ **OMNIA® II** 8204 • • • • • 8254 500 VA • • • . 8206 ٠ . • • • ٠ ٠ 8256 500 VA • • • • 8207 ٠ . • . • . . 8257 500 VA • • • **HYAMP**[®] 3240 • HypotMAX[®] 7705 ٠ 7710 • 7715 • 7720 ٠ LINECHEK[®] II 620L ٠

Not sure which instrument is right for your application?

Use our product selection tool to identify the instrument that satisfies your testing requirements. Go to **arisafety.com** and follow the link to the **Product Selection Tool.**



USB











GPIB



Multiplexer



Multiplexer



Autoware®3

Compatible



WithStand

Compatible

Power Source

Recommended

Hypot [®]									
3805	•							•	
3865	•							•	
3870	٠							•	
HypotULTRA®									
7800	•	•	Opt.	Opt.		•	•	•	
7804	•	•	Opt.	Opt.		•	•	•	
7820	•	•	Opt.	Opt.	•	•	٠	•	
7850	•	•	Opt.	Opt.	•	•	•	•	
7854	٠	•	Opt.	Opt.		•	•	•	
OMNIA® II									
8204	٠	•	Opt.	Opt.	•	•	•		
8254	•	•	Opt.	Opt.	•	•	•		
8206	٠	•	Opt.	Opt.		•	•		•
8256	•	•	Opt.	Opt.		•	•		•
8207	٠	•	Opt.	Opt.		•	•		
8257	•	•	Opt.	Opt.		•	•		
HYAMP®									
3240	•								
HypotMAX®									
7705	•	•		Opt.					
7710	•	•		Opt.					
7715	•	•		Opt.					
7720	•	•		Opt.					
LINECHEK [®] II									
620L	•	•	Opt.	Opt.		•	•		•


MedTEST is the most comprehensive Electrical Safety Compliance test system in the industry designed exclusively for medical applications. Customize it to meet your specific medical safety testing needs in order to comply with standards such as UL60601, IEC60601-1, EN60601-1, UL2601, and IEC601-1. See page 24 for more details.



Our Hypot[®] Series raises the bar for production line Hipot testing. Improve traceability with onboard data storage and easily transfer test result data and test settings via convenient front panel USB. Take the guesswork out of your production line with the direct barcode connection to quickly associate products with pre-programmed test files. We've included advanced features like improved security and a touch screen interface that provides custom pop-up prompts displayed before each test step. We've dramatically reduced the weight and footprint of the Hypot[®] Series to make safety compliance a less strenuous ordeal. Quickly interconnect with the HYAMP® Series to form a complete safety compliance system.



Find the Model that Fits Your Testing Needs



SAFETY & PRODUCTIVITY **FEATURES**







SmartGFI® **Remote Safety** Interlock Automatic Easily disable operator shock HV output protection

Data Transfer Easily import/ export test files and data via USB







Barcode Multiple Capability Languages Direct barcode Multi-Language connection user interface

PLC Remote Basic PLC relay control









Prompt & Hold Provides alerts & instructions between tests

Advanced User Security Customize ID & password protection

Interconnection Interconnect with HYAMP® to form a complete test system





Ramp-HI® Reduce ramp time during DC Hipot

Charge-LO® Confirms proper DUT connection

FailCHEK™ Confirms failure detection





Accredited My Menu Cal Customize your Accredited own shortcut calibration menu options available

On Board Data Storage Save up to

Hypot[®] Series

INPUT SPECIFICA	TIONS				INSULATION RESIST	ANCE TEST MOD		
Voltage	100 – 120 VAC / 20	0 – 240 VAC ± 10)% Auto	o Range	Voltage Setting	Range: Resolution:	30 – 1,000 VDC 1 V	
Frequency	50/60 Hz ± 5%					Accuracy:	± (2% of setting + 5 V)	
Fuse	3.15 A, Fast Blow 2	50 VAC			Resistance Display	-	1 – 50,000 ΜΩ	
DIELECTRIC WITH	ISTAND TEST M	ODE				Resolution: 30 – 99 VI		
Output Rating	3805/3865/3870	6 kVA @ 7.5 mADC (3865/3870 only)				MΩ MΩ 0.001 1.000 – 1.9 0.01 2.00 – 199 0.1 20.0 – 199	292.00 - 19.9910.00 - 99.99920.0 - 199.9100.0 - 999.9	
Maximum Limit	3805/3865/3870		Range: lution:	0.00 – 20.00 mA 0.01 mA		1 200 – 10,0 Accuracy:		
		Resol	Range: lution: uracy:	0 – 7500 μA 1 μA AC and DC ± (2% of setting + 2 counts)			30 – 499 V and 1.00–999.9 MΩ 500-1000 V g + 2 counts) for 1.00 – 999.9 MΩ g + 2 counts) for 1000 – 9999 MΩ	
Minimum Limit	3805/3865/3870		ange: lution:	0.000 – 9.999 mA 0.001 mA	HI & LO-Limit		ng + 2 counts) for 10000 – 50,000 MΩ 0, 1.00 – 99.99 MΩ (0=OFF, HI-Limit ONLY)	
		Resol	lange: lution: uracy:	0.0 – 999.9 μA 0.1μA AC and DC ± (2% of setting		Resolution:	0.01 MΩ 1000-50000 1 MΩ	
Arc Detection	Range:	1-9, ON/OFF Se		+ 2 counts)		Range: Resolution:	100.0 – 999.9 ΜΩ 0.1 ΜΩ	
Ground Fault	GFI Trip Current: 4			ixed		Accuracy:	At test voltage 500-1000 V ± (2% of setting + 2 counts) for 1.00 – 999.9 MΩ	
Interrupt	HV Shut Down Spe	ed: < 1 msec				± (5% of setting + 2 counts) for 1000 – 9999 M! ± (15% of setting + 2 counts) for 10000 – 50,000 MΩ		
Current Display	3805/3865/3870		nge 1: nge 2:	0.000 – 4.000 mA 3.50 – 20.00 mA	Charge-LO	Range:	0.000 – 3.500 µA DC or Auto Set	
		Rai	nge 1: nge 2:	0.0 μA – 400.0 μA 0.350 mA – 4.000 mA	Ramp Timer	Range:	Ramp-Up: 0.1 – 999.9 sec Ramp-Down: 0, 1.0 – 999.9 sec, (0=OFF)	
			nge 3:	3.50 mA – 7.50 mA	Delay Timer	Range:	0.5 – 999.9 sec (0=OFF)	
		Acc	uracy:	All Ranges ± (2% of reading + 2 counts)	Dwell Timer	Range:	0, 0.5 – 999.9 sec (0=continuous)	
DC Output Ripple	\leq 5% Ripple rms at	6 kVDC @ 7.5 m/	A Resis	tive Load	GENERAL SPECIFICA			
RAMP-HI Selectable	Range: 0.0 – 7,500	µA, User Selecta	ble		Remote Control and Signal I/O		t, Hardware Interlock, File Recall il, Test-in-Process, Reset-Out, Start-Out	
Charge-LO	0 – 350 µA DC or A	uto Set			Vmax	Displays the maxin a breakdown	num voltage value recorded during	
Discharge Time	< 50 msec for no lo The maximum cap				lmax	Displays the maxin	num leakage current value read during a test	
	1μF < 1KV 0.75μF < 2KV	0.08µF < 4KV 0.04µF < 5KV 0.015uF < 6KV			Memories	50 steps 1500 test results		
AC Voltage	Sine Wave, Crest F				Interface	USB standard		
Waveform/ Frequency	Range:	50 or 60 Hz, Us	er Sele	ctable	Language		l Chinese, Simplified Chinese, Turkish, sh, German, French	
Dwell Timer	Range:	AC 0, 0.2-999.9 DC 0, 0.4-999.9			Security	Multiple user setu	ps with ID and password	
Ramp Timer	Range:	DC 0, 0.4-999.9 sec (0=Continuous) Ramp-Up: 0.1 – 999.9 sec Ramp-Down: AC 0.0 – 999.9 sec DC 0, 1.0 – 999.9 sec, (0=OFF)		Dimensions (W x H x D)	3805/3865/3870:	8.5" x 3.5" x 11.9" (215 mm x 88.1 mm x 300 mm)		
Ground Continuity Current	DC 0.1A ± 0.01 A, f	ixed			Weight	3805/3865/3870:	12 lbs (5.46 kgs)	
Ground Continuity Maximum Limit Minimum Limit	Range: Resolution: Accuracy:	0.00 – 1.50 Ω 0.01 Ω ± (3% of setting	g + 0.02	2 <u>Ω</u>)	a better indication of the ir to the lowest resolution of	nstrument's capabilit the display for a give	ions using "counts" which allows us to provide ies across measurement ranges. A count refers en measurement range. For example, if the	
Ground Continuity Auto Offset	Range: Resolution: Accuracy:	0.00 – 0.50 Ω 0.01 Ω ± (3% of setting	g + 0.02	2 Ω)	resolution for voltage is 1V			

HypotULTRA®

The Most Flexible and Feature-Rich Automated Dielectric Analyzer Available



Our HypotULTRA® models provide all the tools you need to modernize your production line with best-in-class 4-in-1 test capability and a slim 2U design. We've added 40A AC Ground Bond test capability to HypotULTRA's already impressive feature list for manufacturers that aim to adopt best testing practices without sacrificing productivity. Whether you're looking to improve traceability with onboard data storage, increase efficiency with our intuitive touch screen interface and direct barcode scanner connection, or automate with a variety of communication interfaces, HypotULTRA was designed to take your production line to the next level.



•

Find the Model that Fits Your Testing Needs

•

.



500 VA*

•

•

500 VA*





Continuity

.


.

•









PLC Remote Basic PLC	Negative DC Hipot
relay control	Reverse



*Meets 200 mA short circuit requirements





SAFETY & PRODUCTIVITY FEATURES





Remote Safety Interlock SmartGFI[®] Automatic Easily disable operator shock HV output protection

Data Transfe Easily import/ export test files and data via USB







Barcode Multiple Capability Languages Direct barcode Multi-Language connection user interface

Ground Bond Voltage Drop Monitor voltage drop vs resistance





Internal

ProVOLT[®] Multiplexer Multi-dwell cycles at Available with different optional HV multiplexer voltages for ACW/DCW/IR (4 or 8 ports)

Modular Multiplexer Compatible with SC6540 multiplexers



failure

•

Advanced

User Security

Customize ID

& password

protection



FailCHEK™ Confirms

Prompt & Hold Provides alerts & instructions detection between tests

Autoware®3 Advanced Automation Control

Ramp-HI[®]

Reduce ramp

time during

DC Hipot



Software

Charge-LO® Confirms proper DUT connection

On Board Data

polarity

DC Hipot

(optional)

7800*

7804

7820

7850

7854

HypotULTRA® Series

Note of the set	INPUT SPECIFICA				INSULATION RESISTA	NCE MODE	(Models 7800/7804/7850 & 7854 Only)
ProcessorStorie 1::Storie 1:::Storie 1:::Storie 1:::Storie 1:::Storie 1::::Storie 1::::Storie 1::::Storie 1::::Storie 1:::::Storie 1:::::Storie 1:::::Storie 1:::::::Storie 1::::::::::Storie 1::::::::::::::::::::::::::::::::::::	Voltage	100 – 120 VA	C / 200 – 240	VAC ± 10% Auto Range		Maximum >	20 mA peak
Fire7 monormal7 monormal6 monormal6 monormal7	Frequency	50/60 Hz ± 5	%		and LO-Limit		
AC: WITH STAND Example Result Res	Fuse	7804	/7820/7850:	6.3A, Slow Blow 250 VAC			
			7800/7854:	15A, Fast Blow 250 VAC		Range:	100.0 ΜΩ – 999.9 ΜΩ
Output Value Participant Value Participant Participant Service Control Value Participant Participant Service Participant Participant Service Participant Participant Service Participant Participant Service Participant Participant Service Participant Participant Service Participant Participant Service Partitipant Service Participant Service Participant Service Pa	AC WITHSTAND 1	EST MODE	(All Models	;)			
Output Water Slob 11: 19: bit Streeter Resp 0 11: 99: 99: 4: Output Water 11: 99: 99: 4: Resp 0 10: 99: 99: 4: Utput Water Resp 0 0: 99: 99: 4: Resp 0 0: 99: 99: 4: Water Resp 0: 00: 19: 99: 99: 4: Resp 0: 00: 19: 99: 99: 4: 0: 99: 99: 4: 0: 99: 99: 4: Resp 0: 00: 19: 99: 91: 91: 91: 91: 91: 91: 91: 91	Output Voltage	Resolution:	1 VAC			Range: Resolution:	1,000 MΩ – 50,000 MΩ 1 MΩ
Output NegationSize Varge Course-Texture - 1.3 - 1 SRange Deam TimerRange Dea	Output Frequency	50/60 Hz ± 0	.1%, User Sele	ction	Ramp Up Timer	,	_
Output RegioneInitiant StateInitiant StateInitiant StateInitiant StateInitiant StateUbility ThereRegioneRegi	Output Waveform	Sine Wave, C	Crest Factor =	1.3 – 1.5		-	
Handball Filtering Second Second control Second contro Second contr	Output Regulation	± (1% of outp	out + 5V)				
key is all loss of the second process of the second proces of the second proces of the second process of the		Total		0.000 – 9.999 mA 0.001 mA	Delay Timer		
$ \frac{1}{1000} + $				10.00 – 30.00 mA (10 – 99.99 mA, Models	Charge-LO	0.000 - 3.50	0 μA or Auto Set
Image: Problem in the second 2000/2004 and 2004 and			Resolution: Accuracy:	0.01 mA ± (2% of setting + 2 counts) 7804/7820/7850	CONTINUITY TEST MO	DDE (All Mo	dels)
Result Accord Componentiation Result<		Real		0.000 – 9.999 mA		1 A for 0.000 0.01 A for 10	0 – 1.000 Ω, 0.1 A for 1.01 – 10.00 Ω 0.01 – 100 Ω, 0.001 A for 101 – 1,000 Ω
$ \begin{array}{ $			Range: Resolution:	10.00 – 30.00 mA (10 – 99.99 mA 7800/7854) 0.01 mA	& Min	Resolution:	0.001 Ω
Delit Time Range: 0.02-9999 sec (0-Continuous) Ground Continuity Current: 0.14 ± 0.01.4, fixed Current Resultion: 1.1% of setting = 3 counts) Current Max: Ground Feestinace: 10.01 ± 0.10.10.10.10.10.10.10.10.10.10.10.10.10						Resolution:	0.01 Ω
$ \begin{array}{ $	•	-					
CurrentMax. Ground Resistance: $1.0 \Omega + 0.1 \Omega$ Arc DetectionTo Second PeriodTo Second PeriodArc DetectionRange: $1 - 9$ ranges (9 is most sensitive)Period <td< td=""><td></td><td></td><td></td><td></td><td></td><td>Resolution:</td><td>0.1 Ω</td></td<>						Resolution:	0.1 Ω
Are DetectionRange1 - 9 ranges (9 is most sensitive)1 - 0 ranges (9 is most sensitive) $1 \odot C$ DC WITHSTAND TEST NOTEWoodels 7800/7804/7850 & 7854 Only)Range $1 \odot C$ $1 \odot C$ $A = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = $	-						
DC WITH STAND TEST MODE (Models 7800/7804/7850 & 7854 Only) Range: Resolution: Accuracy: 2 L% of setting + 5V) Range: 2 L% of setting + 5V) Range: 2 L% of setting + 5V) DC Output Voltage Resolution: Accuracy: 2 L% of setting + 5V) Def (MUT) 2 L% of setting + 5V) Def (MUT) 2 L% of setting + 5V) DC Output Ripple 4% (6 K/V) Accuracy: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 10 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 2 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 2 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 2 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 2 counts). Resistance Output Voltage (MUC) Resolution: 2 L% of setting + 2 counts). Resistance Output Voltage (MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 MO - 000 A 0 - 500 mC 2 MUC) Resolution: 1 M						Resolution:	1Ω
Output Voltage Recolution: Range Voltage 0.000 VDC Voltage Recolution: Voltage 12 Recolution: Recolution: 12 Recolution: Recolution: 12 Recolution: DC Output Rippi All and LO-Limit Recolution: Range Voltage 0.000 - 0.099 µA Accuracy 0.000 - 0.099 µA Accuracy 0.000 - 0.999 µA Accuracy 0.000 - 0.900 µA Accuracy 0.000 µA Accuracy	DC WITHSTAND	EST MODE	(Models 78	00/7804/7850 & 7854 Only)			-
Number Parket and the sensitive Load) Duell Timer Range: 0.04-9999 sec (0-Continuous) C Output Ripple -4% (6 KV)	Output Voltage	Range:	Range: 0 – 6000 VDC			Resolution:	1Ω
Hi and LO-Limit Range: Accuracy: Accuracy: Accuracy: a (2% of setting + 10 counts), Low Range is ON GROUND BOND TEST MODE (Model × 7854 Only) Value 10 (000 µ A (accuracy): a (2% of setting + 10 counts), Low Range is ON Range: (000 µ A (accuracy): a (2% of setting + 10 counts), Low Range is ON Range: (000 µ A (accuracy): a (2% of setting + 10 counts), Low Range is ON Range: (000 µ A (accuracy): a (2% of setting + 2 counts) Range: (000 µ A (accuracy): a (2% of setting + 2 counts) 000 µ A (accuracy): a (2% of setting + 2 counts) Range: (000 µ A (accuracy): a (2% of setting + 2 counts) 000 µ A (accuracy): a (2% of setting + 2 counts) Range: (000 µ A (accuracy): a (2% of setting + 2 counts) 000 µ A (accuracy): a (2% of setting + 2 counts) Range I (000 - 999 µ A (accuracy): a (2% of setting + 2 counts) 1000 - 999 µ A (accuracy): a (2% of setting + 2 counts) Range: (00 - 4000 A (accuracy): a (2% of setting + 2 counts) 001 µ A (accuracy): a (2% of setting + 2 counts) Range I (000 - 999 9 µ A (accuracy): a (2% of setting + 2 counts) 000 µ A (accuracy): a (2% of setting + 2 counts) Range: (00 - 4000 A (accuracy): a (2% of setting + 2 counts) 001 µ A (accuracy): a (2% of setting + 2 counts) Range I (000 - 999 9 sec, Low Range is ON (accuracy): a (2% of setting + 2 counts) 0.1 µ A (accuracy): a (2% of setting + 2 counts) 0.1 µ A (accuracy): a (2% of setting + 2 counts) Range I (000 - 100 - 000 A (accuracy): a (2% of setting + 2 counts) 0.1 µ A (accuracy): a (2% of setting + 2 counts) 0.1 µ A (accuracy): a (2% of set				ing + 5 V)	Dwell Timer	,	-
Resolution 0.001 µA Current Range: 3.00 - 8.00 VAC Resolution: 0.001 - 9399 µA Current Resolution: 0.01 A Resolution: 0.001 - 9399 µA Current Resolution: 0.01 A Resolution: 0.01 µA Current Resolution: 0.01 A Resolution: 0.01 µA Current Resolution: 0.01 A Resolution: 0.01 µA Resolution: 0.01 µA Resolution: 0.00 - 9399 µA Resolution: 0.01 µA Resolution: 0.00 - 9399 µA Resolution: 0.01 µA Resolution: 1.00 - 20.000 µA range (7804/54) Resolution: 1.00 - 10.00 A, 0 - 200 mC Resolution: 1.00 - 20.000 µA range (7804/54) Resolution: 1.00 - 150 m G ra 0.01 - 40.00 A Resolution: 1.00 - 20.000 µA range (7804/54) Resolution: 1.00 - 150 m G ra 0.01 - 40.00 A Resolution: 1.00 - 20.000 µA range (7804/54) Resolution: 1.00 - 150 m G ra 0.01 - 40.00 A Resolution: 1.00 - 20.000 µA range (7804/54) Resolution: 1.00 - 150 m G ra 0.01 + 40.00 A <	DC Output Ripple	<4% (6 KV/10	0 mA at Resist	ive Load)	Resistance Offset	Range:	0.000 – 10.00 Ω
Range Resolution1000 - 9.999 µA AccuracyCircuit Voltage)Resolution Accuracy0.01 VAC AccuracyRange Resolution1000 - 9.999 µA Accuracy21% of setting + 10 counts), Low Range is ONDup M AccuracyRange 21% of setting + 2 counts)Range Resolution100 - 9.999 µA Accuracy100 - 9.999 µA Accuracy100 - 9.000 A Resolution0.01 A AccuracyRange Resolution100 - 9.999 µA Accuracy100 - 9.999 µA Accuracy100 - 9.000 A accuracy0.01 0.00 A ResolutionRange Resolution100 - 9.999 µA Accuracy100 - 9.000 µA accuracy100 - 10.00 A accuracy0.01 0.00 A ResolutionRange Resolution100 - 0.000 µA range (780/56) 1 µA Accuracy100 - 10.00 µA accuracy0.01 - 9.99 µA AccuracyRange Resolution100 - 0.000 µA range (780/56) 1 µA Accuracy100 - 10.00 µA accuracy0.01 - 9.90 µA accuracyRange Range Doubly Timer0.4 - 9.99 sec, Low Range is OF 1 µA AccuracyResolution1.00 - 10.00 µA accuracyRange Doubl Timer0.4 - 9.99 sec, Low Range is OF 1 µA AccuracyResolution0.0 - 5.90 mG accuracyRange Doubl Timer0.4 - 9.99 sec, Low Range is ONResolution1.00 accuracyRange Doubl Timer0.4 - 9.99 sec, Low Range is OF 1.00 - 10.01 - 9.000 µA accuracyResolution0.0 - 2.90 mG accuracyRange Dubl Timer0.4 - 9.99 sec, Low Range is ONResolution1.00 accuracyResolutionRange Dubl Timer0	HI and LO-Limit	Resolution:	0.0001 µA		GROUND BOND TEST	MODE (Mo	dels 7804 & 7854 Only)
Accuracy:#c30ut0bi:100 - 000 µA Resolution:001 µA Accuracy:Range:100 - 90 99 µA Accuracy:Range:100 - 100 0 A Accuracy:0 - 40 00 A Accuracy:Range:100 - 90 99 µA Accuracy:Range:100 - 100 0 A Accuracy:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 100 A Accuracy:0 - 200 mQ A ange i ADRange:0 - 200 mQ A ange i ADRange:0 - 200 mQ A ange i ADRange0 - 200 mQ A ange i ADRange i ADRange i ADRange i ADRange i ADRange i ADADRange i ADADRange i ADADRange i ADRange i AD <td></td> <td>Range:</td> <td>1.000 – 9.999</td> <td></td> <td></td> <td>Resolution:</td> <td>0.01 VAC</td>		Range:	1.000 – 9.999			Resolution:	0.01 VAC
$ \begin{array}{ c c c } \hline \mbox{Recolution} & 0.01 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.01 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.01 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.01 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -999 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -999 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -999 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -999 \ \muA \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -20 \ 0.00 \ Ma \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -20 \ 0.00 \ Ma \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -20 \ 0.00 \ Ma \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -20 \ 0.00 \ Ma \\ \hline \mbox{Recolution} & 2 \ 0.00 \ -20 \ 0.00 \ Ma \\ \hline \mbox{Recolution} & 1 \ Ma \\ \hline \mbox{Recolution} & 1$		Accuracy:	± (2% of sett		Output Current	Range: Resolution:	1.00 – 40.00 A 0.01 A
$ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{2} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \frac{1}{4} \left(2 \circ \operatorname{disting}_{2} + 2 \operatorname{counts} \right) $ $ \frac{1}{4} \operatorname{Accuracy}_{2} = \operatorname{Accuracy}_{2} = \operatorname{Accuracy}_{2} = \operatorname{Accuracy}_{2} = \operatorname{Accuracy}_{2} = Accuracy$		Resolution: Accuracy:	0.01 µA ± (2% of sett	ing + 10 counts), Low Range is ON	Maximum Loading	1.00 – 10.00	A, 0 – 600 mΩ
kange: 1,000 - 20,000 µA range (7800/50) Resolution: 0600 mG for 1.00 - 10.01 A mG Range: 1,000 - 20,000 µA range (7800/50) 1µA mage (7800/50) 1µA Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.40 mG for 1.00 - 10.01 A mG mage (7800/50) Accuracy: Range: 0.10 - 999 sec, Low Range is ON Range: 0.10 - 9999 sec, Low Range is ON Owell Timer Range: 0.10 - 9999 sec, Low Range is ON Owell Timer Range: 0.10 - 9999 sec, Low Range is ON Owell Timer Range: 0.10 - 9999 sec, Low Range is ON Owell Timer 0.0 - 200 mG 1 for 100 + 9999 sec, Low Range is ON Owell Timer 0.0 - 200 mG 1 for 100 + 9999 sec, Low Range is ON Owell Timer 0.0 - 200 mG 1 for 100 + 100 + 9999 sec, Low Range is ON Owell Timer 0.0 - 200 mG 1 for 100 + 10		Resolution:	0.1 µA		HI and LO-Limit		
Arr PownInffS = 999.9 sec, Low Range is ONResolution:1 mΩ Accuracy:1 mΩ 4(3% of setting + 3 counts)Ramp Down TimerRange:0,0.1.0 - 999.9 sec (0=OFF)Dwell TimerRange:0,0.4 - 999.9 sec (0=Continuous) 0,1.0 - 999.9 sec (0=Continuous) 0,0.0 - 90.1 - 90.0 NDE of Auto Set 0,0.0 - 90.1 - 90.0 NDE of Auto SetDewell Timer Nemory 0,0.0 - 90.0 NDE of Auto SetResolution 0,0.0 - 90.0 NDE of Auto SetMaximum Capacitive Load ConderImp of 1 (% 100 - 6,000 / PC of Set W) 0,0.0 (% 1 = 5 kW) 0,0.0 (% 1 =		Resolution:	1,000 – 10,0 1 µA	00µA range (7800/50)			$0-600~m\Omega$ for 1.00 – 10.01 A 1 m Ω
Ramp Down TimerRange:0.0, 1.0 - 999.9 sec (0=C)F)Dwell TimerRange:0.0.5 - 999.9 sec (0=Continuous) 0, 1.0 - 999.9 sec, Low Range is ONDwell TimerRange:0.0.64 - 999.9 sec (0=Continuous) 0, 1.0 - 999.9 sec, Low Range is ONDwell TimerRange:0.0.5 - 999.9 sec (0=Continuous) Milliohm OffsetRamp-HI SelectableRange:0 - 20 m A selectableVoltage Offset0 200 mJCharge-LORange:0.0 - 350.0 µ A DC or Auto SetGENERAL SPECIFICATUSDischarge Time<0.0 + 350.0 µ A DC or Auto SetMemory2,000 steps. Job steps per test file max 100,000 test - sultsMaximum Capacitive Load.0.0 µ F < 4 kV 0.0 µ F < 5 kV0.0 µ F < 4 kV 0.0 µ F < 5 kVMemory2,000 steps. Job steps per test file max 100,000 test - sultsMaximum Capacitive Load.0.0 µ F < 4 kV 0.0 µ F < 5 kV0.0 µ F < 4 kV 0.0 µ F < 5 kVMemory2,000 steps. Job steps per test file max 100,000 test - sultsMaximum Capacitive Load.0.0 µ F < 4 kV 0.0 µ F < 5 kV.0.0 µ F < 4 kV 0.0 µ F < 5 kVMemory2,000 steps. Job steps per test file max 100,000 test - sultsMilliohm Offset.0.0 µ F < 4 kV 0.0 µ F < 5 kV.0.0 µ F < 4 kV 0.0 µ F < 5 kVMemory2,000 steps. Job steps per test file max 100,000 test - sultsMaximum Capacitive Load.0.0 µ F < 4 kV 0.0 µ F < 5 kV.0.0 µ F < 6 kVMemory2,000 steps. Job steps per test file max 100,000 test - sultsMilliohm Offset.0.0 µ F < 1 kV 0.0 µ F < 5 kV.0.0 µ F < 6 kV.0.0 µ F < 5 kVMemory2,000 steps. Jo	Ramp Up Timer	Range:				Resolution:	1 mΩ
Dwell TimerRange: 0, 0.4 - 999, 9 sec (0=Continuous) 0, 10 - 999, 9 sec, Low Range is ONMilliohm Offset $0 - 200 \text{ m}$ Ramp-HI SelectableRange:0 - 20 m A selectableVoltage Offset $0 - 200 \text{ m}$ Charge-LORange:0.0 - 350.0 μ A DC or Auto SetGENERAL SPECIFICATIONSDischarge Time< 50 ms or Load, < 100 ms for capacitive loadMemory $2,000$ steps, 200 steps per test file max 100,000 test resultsMaximum Capacitive Load $1\mu F < 1kV$ 0.04 $\mu F < 5 kV$ $0.0 \mu F < 4 kV$ 0.04 $\mu F < 5 kV$ Memory $2,000$ steps, 200 steps per test file max 100,000 test resultsMaximum Capacitive Load $1\mu F < 1kV$ 0.05 $\mu F < 2 kV$ $0.0 \mu F < 4 kV$ 0.04 $\mu F < 5 kV$ Memory $2,000$ steps, 200 steps per test file max 100,000 test resultsMaximum Capacitive Load $1\mu F < 1kV$ 0.05 $\mu F < 2 kV$ $0.0 \mu F < 4 kV$ 0.015 $\mu F < 6 kV$ Memory $2,000$ steps, 200 steps per test file max 100,000 test resultsMaximum Capacitive Load $1\mu F < 1kV$ 0.05 $\mu F < 2 kV$ $0.0 \mu F < 4 kV$ 0.015 $\mu F < 6 kV$ Memory $2,000$ steps, $2,000$ steps, $2,000$ steps per test file max 100,000 test resultsNISULATION RESTANCEElements (Models 7800/7804/7850 & 7854 Only)Memory $2,000$ steps $2 \times 15.75^{\circ}$ (430 x 88.1 x 400mm)Output Voltage, DeclutionRange: $1/20C$ $4 Cauracy teles100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC1/VDC100,100 VDC$	Ramp Down Timer	Range:	0.0, 1.0 – 999	9.9 sec (0=OFF)	Dwall Timer	,	-
Charge-LORange: $0.0 - 350.0 \ \mu$ A DC or Auto SetGENERAL SPECIFICATIONSDischarge Time<50 ms for $-$ load, <100 ms for capacitive load	Dwell Timer	Range:					U, U.J – YYY.Y SEC (U=Continuous)
Discharge Time $< 50 \text{ ms for } \log < 100 \text{ ms for capacitive load}$ Memory $2,000 \text{ steps}, 200 \text{ steps per test file max} 100,000 \text{ test results}$ Maximum Capacitive Load $1\muF < 1kV$ $0.5 \muF < 2 kV$ $0.0 \muF < 4 kV$ $0.04 \muF < 5 kV$ $0.015 \muF < 6 kV$ Memory $2,000 \text{ steps}, 200 \text{ steps per test file max} 100,000 \text{ test results}$ Arc DetectionRange: $1-9 \text{ ranges} (9 \text{ is most sensitive})$ Memory $2,000 \text{ steps}, 200 \text{ steps per test file max} 100,000 \text{ test results}$ INSULATION RESISTANCE MODE(Models 7800/7804/7850 & 7854 Only)SmartGFI® $0, 0.4 - 5.0 \text{ mA} (0=OFF)$ Output Voltage, DCRange: $10-1,000 \text{ VDC}$ $1 VDC$ Immediate the step step step step step step step ste	Ramp-HI Selectable	Range:	0 – 20 mA se	lectable	Voltage Offset	0.0 - 6.0 V	
$ \begin{array}{ c c c c } \hline Maximum \\ Capacitive Load \\ DC Mode \end{array} & \begin{array}{ c c c c } 1 & 0,0 & 0 & 0 & 0 & 0 & 0 & 0 & 0 & 0 &$	Charge-LO	Range:	0.0 – 350.0 µ	A DC or Auto Set	GENERAL SPECIFICAT	IONS	
$ \begin{array}{ c c c c } \hline Maximum \\ Capacitive Load \\ DC Mode \\ \hline O.75 \ \mu\ F < 2 \ k' \\ 0.5 \ \mu\ F < 3 \ k' \\ 0.5 \ \mu\ F < 3 \ k' \\ 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < 6 \ k' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F < \ K' \\ \hline 0.015 \ \mu\ F \ F \ F \ K' \\ \hline 0.015 \ \mu\ F \ F \ K' \ K' \ K' \ K' \ K' \ K' \ $	Discharge Time	< 50 ms for r	no load, < 100	ms for capacitive load	Memory		
Arc Detection Range: 1-9 ranges (9 is most sensitive) Interface Standard: USB, RS-232 Optional: GPIB (IEEE-488.2), Ethernet or USB Printer INSULATION RES: DC Image: 10-1,000 VDC 1/VDC ± (2% of setting + 2 counts) SmartGFI® 0.04-5.0 C=OFF Weight 7800: 45 lbs (20.4 kg) 7804: 41 lbs (18.6 kg) 7820: 34 lbs (15.4 kg) 7820: 34 lbs (15.4 kg) 7820:	Capacitive Load	0.75 µF < 2 k	:V 0.04iµF∢	< 5 kV	Mechanical		
INSULATION RESISTANCE MODE (Models 7800/7804/7850 & 7854 Only) SmartGFI® 0, 0.4 - 5.0 mA (0=OFF) Output Voltage, DC Range: resolution: 10 - 1,000 VDC 1 VDC ± (2% of setting + 2 counts) Dimensions (W x H x D) 16.92" x 3.50" x 15.75" (430 x 88.1 x 400mm) Weight 7800: 7804: 45 lbs (20.4 kg) 7804: 41 lbs (18.6 kg) 7820: 34 lbs (15.4 kg) 7850:		•			Interface		
Output Voltage, DC Range: Resolution: 10-1,000 VDC 1 VDC ± (2% of setting + 2 counts) Dimensions (W x H x D) 16.92" x 3.50" x 15.75" (430 x 88.1 x 400mm) Weight 7800: 7804: 41 lbs (18.6 kg) 7820: 34 lbs (15.4 kg) 7820: 35 lbs (15.9 kg)		-	-		SmartGFI®		
DC Resolution: Accuracy: 1 VDC ± (2% of setting + 2 counts) Weight 7800: 7804: 45 lbs (20.4 kg) 7804: 45 lbs (20.4 kg) 7804: 45 lbs (15.4 kg) 7804: 45 lbs (15.4 kg) 7850: 7804: 41 lbs (18.6 kg) 7820: 7804: 41 lbs (15.4 kg) 7850: 7804: 1 lbs (15.4 kg) 7804: 1 lbs (15.4 kg) 1 lbs (15.4 kg) 7804: <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>							
Range: 1,001 – 6,000 VDC 7820: 34 lbs (15.4 kg) Resolution: 1 VDC 7850: 35 lbs (15.9 kg)	DC	Resolution:	1 VDC			7800:	45 lbs (20.4 kg)
Accuracy: $\pm (2\% \text{ of setting} + 5 \text{ V})$ 7854: 46.3 lbs (21 kg)						7820: 7850:	34 lbs (15.4 kg) 35 lbs (15.9 kg)

The Most Advanced Electrical Safety Compliance Analyzer in the Industry

Our OMNIA® II Series is a complete line of multi-function electrical safety compliance analyzers designed to satisfy even the most demanding application requirements. We've included exclusive productivity-enhancing features and the latest in safety technology to make this product line the envy of the industry. With 6 models to choose from, a multi-language menu system and a variety of automation interfaces available, the OMNIA® II is ready for global deployment.

EN 50191

AVAILABLE INTERFACES



SAFETY & PRODUCTIVITY FEATURES





Active Link®

Continuous

test steps



Remote Safety Interlock SmartGFI® Automatic Easily disable operator shock HV output protection

Prompt & Hold Provides alerts & instructions between tests





Multiple Languages Multi-Language power during user interface

My Menu Customize your own shortcut menu





DualCHEK® Simultaneous Hipot and Ground Bond



Internal Multiplexer Available with optional HV multiplexer (4 or 8 ports)

Modular Multiplexer Compatible with SC6540 multiplexers









PLC Remote Basic PLC relay control

FailCHEK™ Confirms failure detection

Cal-Alert[®] Tracks and alerts for calibration



Charge-LO® Ramp-HI®



Arc Detection High frequency filter for corona detection



Automation

Control

Software

Accredited





Ground Bond Monitor



Find the Model that Fits Your Testing Needs

.

.

.



•

•

•

•



Continuity

•

.

.

•



Resistance

٠

٠

٠

•



Current

•

•



Run







•

•

Reduce ramp Confirms time during proper DUT DC Hipot connection





Voltage Drop voltage drop vs resistance

*Meets 200 mA short circuit requirements

500 VA*

500 VA*

500 VA*



8204

8254

8206

8256

8207

8257

INPUT SPECIFICA						
Voltage	115/230 V Aut	o Range, ± 15	% Variation			
Frequency	50/60 Hz ± 5%	50/60 Hz ± 5%				
Fuse	115 VAC, 230 V	VAC – 10 A Slo	w Blow 250 VAC			
DIELECTRIC WITH	ISTAND TES	T MODE				
Output Rating	5 kV @ 50 mAAC 5 kV @ 100 mAAC (Models 825X) 6 kV @ 20 mADC					
Voltage Setting	Resolution: Accuracy:	1 V ± (2% of sett	ing + 5 volts			
HI and LO-Limit	AC Total	Range: Resolution:	0.000 – 9.999 mA 0.001 mA			
		Range: Resolution:	10.00 – 50.00 mA (100.00 mA, models 825X) 0.01 mA			
		Accuracy:	± (2% of setting + 2 counts)			
	AC Real	Range: Resolution:	0.000 – 9.999 mA 0.001 mA			
		Range: Resolution:	10.00 – 50.00 mA (100.00 mA, models 825X) 0.01 mA			
		Accuracy:	\pm (3% of setting + 50 $\mu\text{A})$			
	DC	Range: Resolution:	0 – 999.9 μΑ 0.1 μΑ			
		Range: Resolution:	1,000 – 20,000 μΑ 1 μΑ			
		Accuracy:	± (2% of setting + 2 counts)			
Arc Detection	Range:	1 – 9 (9 is mo	ost sensitive)			
Ground Continuity	Current: DC 0. Max. Ground F		ixed Ω ± 0.1 Ω, fixed			
Ground Fault Interrupt	GFI Trip Curre HV Shut Down		0 mA (AC or DC) s			
DC Output Ripple	≤ 4% Ripple rn	ns at 5 kVDC a	t 20 mA Resistive Load			
Discharge Time	≤ 50 ms No Lo	ad, < 100 ms f	or Capacitive Load			
Max Capacitive Load, DC Mode	1 μF < 1 kV 0.75 μF < 2 kV 0.5 μF < 3 kV		08 μF < 4 kV 04 μF < 6 kV			
AC Output Waveform	Sine Wave, Cre	est Factor = 1.	3 – 1.5			
Output Frequency	Range:	60 or 50 Hz,	User Selection (400/800 Hz optional)			
Output Regulation	± (1% of output voltage rang		no load to full load and over input			
Dwell Timer	Range: Range:		9 sec (0=Continuous) 9 sec (0=Continuous)			
Ramp Timer	Ramp-up: Ramp-Down:		9 sec, DC 0.4 – 999.9 sec .9 sec, DC 0.0 , 1.0 – 999.9 sec us)			
INSULATION RES	ISTANCE TES	ST MODE				
Voltage Setting	Range:	30 – 1000 VE	DC			
HI and LO-Limit	Range: Resolution:	0.05 MΩ – 99 0.01 MΩ	2.99 ΜΩ			
	Range: Resolution:	100.0 MΩ – 9 0.1 MΩ	999.9 ΜΩ			
	Range: Resolution:	1,000 MΩ – 5 1 MΩ (HI-Lim				
Ramp Timer	Ramp-up: Ramp-Down:	0.1 – 999.9 se 0.0, 1.0 – 999	ec 9.9 sec (0=Continuous)			
Delay Timer	Range:	0.5 – 999.9 se	ec (0=Continuous)			

GROUND BOND	TEST MODE	
Output Voltage (Open Circuit Limit)	Range:	3.00 - 8.00 VAC
Output Frequency	Range:	60 or 50 Hz, User Selectable
Output Current	Range: Resolution: Accuracy:	1.00 – 40.00 A 0.01 A ± (2% of setting + 0.02 A)
Maximum Loading	1.00 – 10.00 A, 10.01 – 30.00 A 30.01 – 40.00 A	, 0 – 200 mΩ
HI and LO-Limit	$ \begin{array}{c} \text{O-Limit} & \text{Range:} & 0 - 150 \ \text{m}\Omega \ \text{for} \ 30.01 - 40.00 \ \text{A} \\ & 0 - 200 \ \text{m}\Omega \ \text{for} \ 10.01 - 30.00 \ \text{A} \\ & 0 - 600 \ \text{m}\Omega \ \text{for} \ 1.00 - 10.00 \ \text{A} \\ & \text{Resolution:} & 1 \ \text{m}\Omega \\ & \text{Accuracy:} & \pm (2\% \ \text{of} \ \text{reading} + 2 \ \text{m}\Omega) \\ \end{array} $	
	Range: Resolution: Accuracy:	0 – 600 mΩ for 1.00 – 5.99 A 1 mΩ ± (3% of reading + 3 mΩ)
Dwell Timer	Range:	0.5 – 999.9 sec (0=Continuous)
Milliohm Offset	Range:	0 – 200 mΩ
CONTINUITY TES	T MODE	
Output Current	DC 0.01 A ± 0.0	0001 A
Resistance Display	Range:	0.00 – 10000 Ω
HI and LO-Limit	Range: Resolution:	1: 0.00 – 10.00 Ω 0.01 Ω
	Range 2: Resolution:	10.1 – 100.0 Ω 0.1 Ω
	Range 3: Resolution: Accuracy:	101 – 1,000 Ω 1 Ω ± (1% of reading + 3 counts)
	Range 4: Resolution: Accuracy:	1,001 – 10,000 Ω 1 Ω \pm (1% of reading + 10 counts) (Max Limit: 0=OFF)
Dwell Timer	Range:	0.0, 0.3 – 999.9 sec (0=Continuous)
Milliohm Offset	Range:	0.00 – 10.00 Ω
RUN TEST MODE	(Models 82X	6 & 82X7 only)
DUT Power	Voltage: Current: Range: Resolution: Accuracy:	0 – 277 VAC single phase unbalanced 16 AAC max continuous 0.0 – 277.0 VAC Full Scale 0.1 V ± (1.5% of reading +0.2 V), 30.0 – 277.0 VAC Short Circuit Protection: 23 AAC, Response Time < 3 sec
Delay Time Setting	Range:	0.2 – 999.9 seconds
Dwell Time Setting	Range:	0.1 – 999.9 seconds (0=Continuous)

OMNIA® II Series

			2X6 & 82X7 only)	LEARAGE COM		DE CONTINUED (Models 82X6 & 82X7 only)		
Trip Point Settings	Voltage			Touch Current	Range 1:	0.0 $\mu A \sim 32.0 \ \mu A,$ frequency DC, 15 Hz – 1 MHz		
& Metering	Volt-Hi	Range:	30.0 – 277.0 VAC	Display (rms)	Range 2:	28.0 $\mu A \sim 130.0 \; \mu A,$ frequency DC, 15 Hz – 1 MHz		
	Volt-LO	Resolution: Accuracy:	0.1 V ± (1.5% of setting + 0.2 V), 30.0–277 VAC		Range 3:	120.0 $\mu A \sim 550.0$ $\mu A,$ frequency DC, 15 Hz – 1 MHz		
	Current	_			Resolution for Ranges 1, 2, 3:	0.1 μΑ		
	Amp-HI Amp-LO	Range: Resolution: Accuracy:	0.0 – 16.00 AAC 0.01 A ± (2.0% of setting + 2 counts)		Accuracy for Ranges 1, 2, 3:	DC: 15 Hz < f <100 KHz: ± (2% of reading + 3 counts) 100 KHz < f < 1 MHZ: ± 5% of reading (10.0 μA – 999.9 μA		
	Watts				Range 4:	400 μA ~ 2100 μA, frequency DC, 15 Hz – 1 MHz		
	Power-HI	Range:	0 – 4,500 W		Range 5:	800 μA ~ 8500 μA, frequency DC, 15 Hz – 1 MHz		
	Power-LO	Resolution: Accuracy:	1 W ± (5.0% of setting + 3 counts)		Resolution for Ranges 4 & 5:	1 μΑ		
	Power Factor	Range:	0.000 – 1.000		Accuracy for Ranges 4 & 5:	DC: 15 Hz < f <100 KHz: ± (2% of reading + 3 counts) 100 KHz < f < 1 MHZ: ± 5% of reading (10 µA – 8500 µA)		
	PF-LO	Resolution:	0.001		Range 6:	8.00 mA ~ 10.00 mA, frequency DC 15 Hz – 100 kHz		
	Leakage Current	Accuracy:	± (8% of setting + 2 counts)		Resolution:	0.01 mA		
	Leak-HI Leak-LO	Range: Resolution:	0.00 – 10.00 mA (0=OFF) 0.01 mA		Accuracy:	DC: 15 Hz < f < 100 KHz: ± 5% of reading (0.01 mA -10.00 mA)		
		Accuracy:	± (2% of setting + 2 counts)	Touch Current	Range 1:	0.0 μA ~ 32.0 μA, frequency DC – 1 MHz		
Timer Display	Range: Resolution:	0.0 – 999.9 s 0.1 second	econds	Display (Peak)	Range 2:	28.0 $\mu A \sim 130.0 \ \mu A,$ frequency DC – 1 MHz		
	Accuracy:		ading + 0.05 seconds)		Range 3:	120.0 μA ~ 550.0 μA, frequency DC – 1 MHz		
			82X6 & 82X7 only)		Resolution for Ranges 1, 2, 3:	0.1 μΑ		
DUT Power	Voltage: Current:	0 – 277 VAC 16 AAC max			Accuracy for Ranges 1, 2, 3:	DC: ± (2% of reading + 2 μA) 15 Hz < f < 1 MHZ : ± 10% of reading + 2 μA		
	Voltage Display	Range: Resolution:	0.1 V		Range 4:	400 μA ~ 2100 μA, frequency DC – 1 MHz		
	Short Circuit	Accuracy:	± (1.5% of reading +0.2 V), 30.0 – 277.0 VAC ponse Time < 3 s		Range 5:	1800 A ~ 8500 μA, frequency DC – 1 MHz		
	Protection:		•		Resolution for Ranges 4 & 5:	1 μΑ		
Reverse Power Switch	ON: Reverse pow OFF: Normal	ver	select ON/OFF/AUTO		Accuracy for Ranges 4 & 5:	DC: ± (2% of reading + 2 μA) 15 Hz < f < 1 MHz: ±(10% of reading + 2 μA)		
	AUTO: Automatio		-		Range 6:	8.0 mA ~10.00 mA, frequency DC – 100 KHz		
Neutral Switch	ON/OFF selectio	n for single fau	Ilt condition		Resolution:	0.01 mA		
Ground Switch			ngle fault condition		Accuracy:	DC: ± (2% of reading + 3 counts) 15 Hz < f < 100 KHz: ± (10% of reading + 2 counts)		
Probe Setting	Surface to Surface Surface to Line (F Ground to Line (C	'H – L)		MD Circuit Module	MD1: UL544NP, U MD2: UL544P	MD1: UL544NP, UL484 , UL923, UL471, UL867, UL697		
Touch Current High Limit (rms)	Range: 0.0 µA ~ 999.9 µA 1000 µA ~ 10.00 mA				MD3: IEC 60601-1 MD4: UL1563			
					IEC60598-7 MD6: IEC60990 F	Fig4 U2, IEC 60950-1, IEC60335-1, I, IEC60065, IEC61010 Fig5 U3, IEC60598-1		
					MD7: IEC60950, MD8: IEC60990/	IEC61010-1 FigA.2 (2K ohm) for Run function		

Scope Output Interface BNC type connector on rear panel for Oscilloscope connection

OMNIA® II Series

AC POWER SC	OURCE (82X7	only)				
Output	Power:	630 VA and 500	W Maximum			
	Voltage:	0 – 150.0 V / 0 –	277.0 V			
	Current:		4.20 A maximum for 0 – 150 V range 2.10 A maximum 0 – 277 V range			
	Distortion:		Hz and output voltage within the 80 ~ 140 ge or the 160 ~ 277 VAC at High Range			
	Regulation:	\leq 0.5% + 5 V (resistive load), from no load to full load and Lov Line to High Line (combined regulation)				
	Crest Factor:	> 3				
	Test Timing:	< 350 ms at start	and between			
	Limit:	Steps when internal AC source is ON				
Settings	Voltage	Low Range:	0.0 – 150.0 V			
		High Range:	0.0 – 277.0 V			
		Resolution:	0.1 V			
		Accuracy:	± (1.5% of setting + 2 counts)			
	Frequency A-HI-Limit	Range: Resolution: Accuracy:	45.0 Hz – 99.9 Hz 0.1 Hz ± 0.1% of setting			
		Range: Resolution: Accuracy:	100 Hz – 500 Hz 1 Hz ± 0.1% of setting			
		Range: Resolution: Accuracy:	4.20 A / 2.10 A 0.01 A ± (2% of reading + 2 counts)			
Measurement	t Voltage	Range: Resolution: Accuracy:	0.0 - 277.0 V 0.1 V ± (1.5% of reading + 2 counts)			
		Current Range: Resolution: Accuracy:	0.00 – 16.00 A 0.01 A ± (2% of reading + 2 counts)			
		Power: Resolution: Accuracy:	0 – 4500 1 ± (5% of reading + 3 counts) for PF > 0.100			
		Power Factor: Resolution: Accuracy:	0.000 – 1.000 0.001 ± (8% of reading + 5 counts)			
		Frequency: Resolution: Accuracy:	45 – 500 Hz 0.1 Hz ± 0.1 Hz			

GENERAL SPECI	FICATIONS			
PLC Remote Control	Input: Test, Reset, Interlock, Recall File 1 through 3 Output: Pass, Fail, Test-in-Process			
Safety	Built-in SmartGFI circuit			
Memory	10,000 Steps			
Interface	Standard: USB/RS-232 Optional: Ethernet or GPIB			
Security	Advanced security system with access levels and username/password requirements			
Dimensions (W x H x D)	16.93" x 5.24" x 19.69" (430 x 133 x 500 mm)			
Weight	8204: 82 lbs (37 kg) 8254: 92 lbs (42 kg) 8206/8207: 83 lbs (38 kg) 8256/8257: 103 lbs (47 kg)			

Why We Use Counts Associated Research publishes some specifications using "counts" which allows us to provide a better indication of the instrument's capabilities across measurement ranges. A count refers to the lowest resolution of the display for a given measurement range. For example, if the resolution for voltage is 1V then 2 counts = 2 V.

Specifications subject to change without notice.

HYAMP[®]

The Industry Leading Production Line Ground Bond Instrument

Our HYAMP® Series provides manufacturers with data-driven results and greater test flexibility required in today's complex test environment. Quickly collect test data and test settings from the convenient front panel USB port onto a standard USB flash drive. Use the front panel barcode connection to associate products with preprogrammed test files. Test with greater flexibility by performing either AC Ground Bond or DC Ground Bond at a maximum of 40 A of current. The HYAMP® features a drastically reduced weight and footprint making it the ideal lightweight Ground Bond solution for laboratory and production line testing applications. Easily interconnect with the Hypot[®] Series to form a complete safety compliance system.

CE



Find the Model that Fits Your Testing Needs



AC/DC

3240

AVAILABLE INTERFACES



SAFETY & PRODUCTIVITY FEATURES





Remote Safety Interlock

PLC Remote Basic PLC Easily disable relay control HV output

Data Transfer Easily import/ export test files and data via USB



Barcode Multiple Capability Languages Multi-Language Direct barcode connection user interface

Ground Bond Voltage Drop Monitor voltage drop vs resistance

•





FailCHEK™ Confirms failure detection

Advanced Prompt & Hold User Security **Provides** alerts & instructions Customize ID & password between tests protection





4-Wire

milliohm



Accredited Cal Accredited calibration options available

Interconnection Measurement Interconnect with Hypot® to form More accurate a complete test system measurement



On Board Data Storage Save up to 1,500 Test Results on-board





HYAMP®

INPUT SPECIFICATIO	NS	
Voltage	100 – 120 VA	C / 200 – 240 VAC ± 10% Auto Range
Frequency	50/60Hz ± 5%	6
Fuse	10 A, Slow Bl	ow 250 VAC
GROUND BOND T	EST MODE	
Output Voltage (Open Circuit Voltage)	Range: Resolution: Accuracy:	
Output Frequency	50 or 60 Hz, l	Jser Selectable/DC
Output Current	Range: Resolution: Accuracy:	$\begin{array}{l} 0-150 \ m\Omega \ for \ 30.01 - 40.00 \ A \\ 0-200 \ m\Omega \ for \ 10.01 - 30.00 \ A \\ 0-600 \ m\Omega \ for \ 1.00 - 10.01 \ A \\ 0.1 \ A \\ \pm \ (3\% \ of \ setting + 3 \ counts) \end{array}$
Maximum Loading	Range: Resolution: Accuracy:	1.00 - 10.00 A, 0 - 600 mΩ 10.01 - 30.00 A, 0 - 200 mΩ 30.01 - 40.00 A, 0 - 150 mΩ 1 mΩ ± (2% of setting + 2 counts)
HI and LO-Limit Resistance	Range: Resolution: Accuracy:	$\begin{array}{l} 0-150 \ m\Omega \ for \ 30.01 - 40.00 \ A \\ 0-200 \ m\Omega \ for \ 10.01 - 30.00 \ A \\ 0-600 \ m\Omega \ for \ 1.00 - 10.01 \ A \\ 1 \ m\Omega \\ \pm \ (2\% \ of \ setting + 2 \ counts) \end{array}$
HI and LO-Limit Voltage	Range: Resolution: Accuracy:	0.00 – 6.00 V 0.01 ± (2% of settings + 2 counts)
Dwell Time Setting	Range:	0, 0.5 – 999.9 sec (0=Continuous)
Ω Offset Capability	Range: Resolution: Accuracy:	0 - 100 mΩ 1 mΩ ± (2% of setting + 2 counts)
V Offset Capability	Range: Resolution: Accuracy:	0.00 – 4.00 V 0.01 V ± (2% of setting + 2 counts)
Current Display	Range: Resolution: Accuracy:	0.00 – 40.00 AAC/DC 0.01 AC/DC ± (3% of reading + 1 count)
Voltage Display	Range: Resolution: Accuracy:	0.00 – 8.00 VAC/DC 0.01 AC/DC ± (2% of reading + 2 counts)
Ohmmeter Display	Range: Resolution: Accuracy:	0 - 600 mΩ for 1.00 - 5.99 A 1 mΩ ± (3% of reading + 3 counts)
	Range: Resolution: Accuracy:	0 – 600 mΩ for 6 – 40 A 1 mΩ ± (2% of reading + 2 counts)

GENERAL SPECIFICAT	IONS
Remote Control and Signal I/O	The following input and output signals are provided through two 9 pin D type connectors: Inputs: Test, Reset, Hardware Interlock, File Recall Outputs: Pass, Fail, Test-in-Process, Reset-Out, Start-Out Hardware Interlock (safety)
Memories	50 steps 1500 test results
Interface	USB standard
Language	English, Traditional Chinese, Simplified Chinese, Turkish, Portuguese, Spanish, German, French
Security	Multiple user setups with ID and password
Dimensions (W x H x D)	8.5" x 3.5" x 11.9" (215 x 88.1 x 300 mm)
Weight	11 lbs (5 kg)

Why We Use Counts Associated Research publishes some specifications using "counts" which allows us to provide a better indication of the instrument's capabilities across measurement ranges. A count refers to the lowest resolution of the display for a given measurement range. For example, if the resolution for voltage is 1V then 2 counts = 2 V.

Specifications subject to change without notice.

HypotMAX[®]

The Safest and Most Reliable Automated High Voltage Hipot Instrument Available

Our HypotMAX[®] Series is a complete line of automated Hipot instruments designed to meet the demanding requirements of high voltage applications. We've included our patented SmartGFI® feature for maximum operator safety as well as a variety of advanced features to increase productivity on the production line and in the lab. Set up and run tests with confidence from our intuitive user interface or automate with a PC.

AVAILABLE INTERFACES



SAFETY & PRODUCTIVITY FEATURES





PLC Remote SmartGFI® Basic PLC Automatic operator shock relay control protection

Remote Safety Interlock Easily disable HV output







Arc Detection High frequency filter for corona

detection

Ramp-HI® Reduce ramp time during DC Hipot

Charge-LO[®] Confirms proper DUT connection



Accredited Cal Accredited calibration options available

Autoware Use with automation

software control



Find the Model that Fits Your Testing Needs





00 n -

7705 7710 • 7715 7720 •

HypotMAX[®] Series

INPUT SPECIFICA			
Voltage		± 10%, Single	Phase, User Selection
Frequency	50/60 Hz ± 5%		
Fuse	6.3 A. 250 V	Slow Blow	
DIELECTRIC WITH	ISTAND TES	ST MODE	
Output Rating	7705:	10 kV @ 20 m	AAC
output hatting	7710: 7715: 7720:	12 kV @ 10 m. 20 kV @ 10 m. 20 kV @ 5 mA	ADC AAC
HI-Limit and LO-Limit	7705	Range 1: Resolution: Range 2: Resolution:	0.0 – 9.999 mA 0.001 mA 10.00 – 20.00 mA 0.01 mA
	7710	Range 1: Resolution: Range 2: Resolution:	0.00 – 999.9 μA 0.1 υA 1,000 – 9,999 μA 1 μA
	7715	Range: Resolution:	0.00 – 9.999 mA 0.001 mA
	7720	Range 1: Resolution: Range 2: Resolution:	0.0 – 999.9 μΑ 0.1 μΑ 1,000 – 5,000 μΑ 1 μΑ/step
	77XX	Accuracy:	± (2% of setting + 2 counts)
DC Ramp HI	7710	13 mA peak n	naximum, 10 mADC, ON/OFF selectable
	7720	6.75 mA peak	maximum, 5 mADC, ON/OFF selectable
DC Charge LO	7710/7720	Range:	0.0 – 350 µADC or auto set
Arc Detection	7705	1 – 8 at outpu	it voltage < 7.00 kV it voltage ≥ 7.00 kV
	7710/7720	1 – 9	
	7715	1 – 7 at outpu	It voltage < 15.00 kV It voltage ≥ 15.00 kV
Voltage Display	7705	Range: Accuracy:	0.00 – 10.00 kV Full scale ± (2% of reading + 20 V)
	7710	Range: Accuracy:	0.00 – 12.00 kV Full scale ± (2% of reading + 20 V)
	7715/7720	Range: Accuracy:	0.00 – 20.00 kV Full scale ± (2% of reading + 20 V)
Current Display	7705	Auto Range Range 1: Range 2:	0.000 – 3.500 mA 3.00 – 20.00 mA
	7710	Auto Range Range 1: Range 2: Range 3:	0.0 – 350.0 μΑ 300 – 3500 μΑ 3,000 – 9,999 μΑ
	7715	Auto Range Range 1: Range 2:	0.000 – 3.500 mA 3.00 – 10.00 mA
	7720	Auto Range Range 1: Range 2:	0.0 – 350.0 μΑ 300 – 5,000 μΑ
DC Output Ripple	7710	< 5% Ripple a	nt 12 kV @ 9,999 μA, Resistive Load
	7720	< 5% Ripple a	at 20 kV @ 4,999 μA, Resistive Load
AC Output Waveform	Sine Wave, C	Crest Factor = 1	.3 – 1.5
Output Frequency	Range:	50/60 Hz, Use ± (1% of outp No load to fu	ut + 5 V) from Regulation
Output Regulation	± (1% of outp	out + 10 V) from	n no load to full load
Discharge Timer	7710	No load < 40	0 ms
	7720	No load < 50	0 ms
Dwell Timer		Range: AC Range: DC Range:	0, 0.3 – 999.9 sec (0=Continuous) 0, 0.3 – 999.9 sec or min (0=Continuous) 0, 0.4 – 999.9 sec or min (0=Continuous)
Ramp Timer	7705/7715	Range:	0.3 – 999.9 sec
	7710/7720	Range:	0.4 – 999.9 sec
Ground Continuity	Max. Ground	d Resistance 1	Ω ± 0.1 Ω, fixed

DIELECTRIC WITH	ISTAND TEST MODE
Ground Fault Interrupt	HV Shut Down Speed < 1 ms GFI Trip Current 1 mA max
GENERAL SPECIP	ICATIONS
Memory	50 memories w/ 8 steps per memory
Mechanical	Tilt-up front feet
Interface	Standard: USB, RS-232 Optional: GPIB
Dimensions (W x H x D)	16.93" x 5.24" x 15.75" (430 x 133 x 400 mm)
Weight	7705/7710: 61.65 lbs (28 kg) 7710/7720: 48.9 lbs (22 kg)

Why We Use Counts Associated Research publishes some specifications using "counts" which allows us to provide a better indication of the instrument's capabilities across measurement ranges. A count refers to the lowest resolution of the display for a given measurement range. For example, if the resolution for voltage is 1V then 2 counts = 2 V.

Specifications subject to change without notice.


SC6540

The Patented Multiplexer that Revolutionized Production Line and Laboratory Electrical Safety Compliance Testing

Our patented SC6540 multiplexer pioneered the largest productivity improvement in the electrical safety compliance industry in years. With up to 16 independent high voltage or high current channels in a convenient 2U design, the SC6540 can be customized in 10 different configurations for multi-point Hipot, Ground Bond, Insulation Resistance, and Leakage Current testing. Configure the SC6540 according to your needs, and interface with your OMNIA® II, HypotULTRA® or LINECHEK® II instrument to improve production line throughput or expand lab testing capability. Operate from the front panel of your AR instrument or utilize a variety of automation interfaces for direct PC control.



Find the Model that Fits Your Testing Needs



AVAILABLE INTERFACES



PRODUCTIVITY ENHANCING FEATURES





test system



BatchTEST® Simultaneous DUT testing with AW2 Interconnection Autoware®3 Interconnect Advanced with the Automation HypotULTRA®, Control UNNIA® II or Software LINECHEK® II to form a complete

FOR USE WITH THE FOLLOWING TESTS







AC Hipot



Ground Bond







Ground Continuity

Insulation Resistance



Available in both main and secondary configurations

MODULAR MULT	IPLEXER SPECIFICATIONS	
Input (Main only)	115 VAC (± 10%), 50/60 Hz, single phase 230 VAC (± 10%), 50/60 Hz, single phase User selectable	
Fuse (Main only)	250 V/2 A/fast-blow	
PC Control (Main only)	Standard: USB, RS-232 Optional: Ethernet, GPIB	
Multiplexer Control	Main: One Multiplexer bus output controls, up to 4 additional secon Secondary: One output and one input	daries
Maximum HV Rating	5 kV AC and DC	
Maximum HC Rating	40 A	
Number of Possible Channels	8 or 16	
HV Output	100' reel HV cable rated for up to 30 kV Terminations with 8 HV connectors	
GND Output	20 terminals provided, to accept 10/12 AWG Terminations hook-up wire (user supplied wire)	
Temperature	32° – 104° F (0° – 40° C)	
Humidity	0 – 80%	
Altitude	6,560 ft. (2,000 m)	
Mechanical	2U with tilt-up front feet	
Dimensions (W x H x D)	17" x 4.07" x 12.96" (432 x 103 x 329 mm)	
Weight	Main: 20.05 lbs. max. (9.09 kg) (with 2 high voltage modules Secondary: 15.45 lbs. max. (7.01 kg) (with 2 high voltage modules	

CONFIGURATIONS

The modular design can be customize to fit your application. In addition to main or secondary control, the SC6540 can be set up in the following configurations: 8 or 16 high voltage channels, 8 or 16 high current channels, and 8 high voltage channels and/or 8 high current channels. Refer to the images for details.

The different configurations (shown below) are indicated by the following alpha designators

 $\begin{array}{l} M-Main Multiplexer\\ H-8 High Voltage Channels\\ HH-16 High Voltage Channels\\ G-8 Ground Bond Channels\\ GG-16 Ground Bond Channels\\ N-Empty Module\\ S-Secondary \end{array}$



MODEL SC6540 HNM*

8 Channel High Voltage Multiplexer



MODEL SC6540 HHM* 16 Channel High Voltage Multiplexer



MODEL SC6540 HGM* 8 Channel High Voltage Multiplexer 8 Channel High Current Multiplexer



MODEL SC6540 GNM* 8 Channel High Current Multiplexer



MODEL SC6540 GGM* 16 Channel High Current Multiplexer

*Also available in secondary configuration

LINECHEK®II

The Fully Automated Leakage Current Instrument that Changed the Industry

Our LINECHEK® II model 620L provides 7 measuring devices (MD's) compliant with international certification bodies as well as a convenient switching network to simulate all 8 required fault conditions, everything you need for full Leakage Current compliance. Utilize the intuitive user interface or control via a PC for more advanced automated applications that require data storage and analysis. The 620L handles up to 40 A of continuous current and can be interfaced to an SC6540 modular multiplexer for multi-point testing. Interconnect the 620L to an OMNIA® II instrument to form a complete electrical safety compliance testing system.



AVAILABLE INTERFACES



SAFETY & PRODUCTIVITY FEATURES







Prompt & Hold Provides alerts & instructions between tests

Active Link® Continuous power during test steps







PLC Remote Basic PLC relay control

Multiplexer Compatible with SC6540 HypotULTRA® to multiplexers form a complete test system



Cal-Alert® Tracks and alerts for calibration

Find the Model that Fits Your Testing Needs



Functional

Run



620L







Interlock

Easily disable HV output

Modular

Interconnection Interconnect with OMNIA® II or

INPUT SPECIFICA	TIONS	
Voltage		C ± 10%, User Selection
Frequency	50/60 Hz ± 5	
Fuse	2 A Slow Blo	
LINE CONDITION		
Reverse Power Switch		ower polarity reversal
Neutral Switch	Neutral swit	ch on/off selection for single fault
Ground Switch		ch on/off selection for class I single fault
PROBE SETTINGS	;	
Surface to Surface	(PH – PL)	
Surface to Line	(PH – L)	
Ground to Line	(G – L)	
LEAKAGE LIMIT S	ETTINGS	
Touch Current High/Low Limit	Range: Resolution:	0.0 μA – 999.9 μA / 1,000 μA – 9,999 μA / 10.00 mA – 20.00 mA 0.1 μA / 1 μA / 0.01 mA
(rms) Touch Current High/Low Limit	Range: Resolution:	0.0 μA -999.9 μA / 1,000 uA – 9,999 μA / 10.00 mA – 30.00 mA 0.1 μA / 1 μA / 0.01 mA
(Peak) DISPLAY		
	R	
Touch Current Display (rms)	Range: Resolution: Accuracy:	$\begin{array}{l} 0.0 \ \mu A - 550 \ \mu A, \ frequency DC, \ 15 \ Hz - 1 \ MHz \\ 0.1 \ \mu A \\ DC: \ 15 \ Hz \leq f \leq 100 \ HHz: \ \pm (2\% \ of \ reading + 3 \ counts) \\ 100 \ HHz \leq f \leq 1 \ MHz: \ \pm 5\% \ of \ reading \ (10.0 \ \mu A - 999.9 \ \mu A) \end{array}$
	Range: Resolution: Accuracy:	400 μ A − 8,500 μ A, frequency DC, 15 Hz − 1 MHz 1 μ A DC: 15 Hz ≤ f ≤ 100 kHz: ± (2% of reading + 3 counts) 100 kHz ≤ f ≤ 1 MHz: ± 5% of reading, (10.0 μ A − 8,500 μ A)
	Range: Resolution: Accuracy:	8.00 mA – 20.00 mA, frequency DC, 15 Hz – 100 KHz 0.01 mA DC: 15 Hz ≤ f ≤ 100 MHz: ± 5% of reading (0.01 mA – 20.00 mA)
Touch Current Display (peak)	Range: Resolution: Accuracy:	0.0 μ A – 550 μ A, frequency DC – 1 MHz 0.1 μ A ± (2% of reading + 2 μ A) 15 Hz ≤ f ≤ 1 MHz, ± 10% of reading + 2 μ A
	Range: Resolution: Accuracy:	400 μ A - 8,500 μ A, frequency DC - 1 MHz 1 μ A ± (2% of reading + 2 μ A) 15 Hz ≤ f ≤ 1 MHz, ± 10% of reading + 2 μ A
	Range: Resolution: Accuracy:	8.00 mA – 30.00 mA, frequency DC – 100 kHz 0.01 mA \pm (2% of reading + 3 counts) 15 Hz \leq f \leq 100 kHz, \pm 10% of reading + 2 counts
MEASURING DEV	ICE MODU	LE
MD1	UL544NP, U	L484 , UL923, UL471, UL867, UL697
MD2	UL544P	
MD3	IEC 60601-1	
MD4	UL1563	
MD5	IEC60990 Fig IEC61010	g4 U2, IEC60950-1, IEC60335-1, IEC60598-1,IEC60065,
MD6	IEC60990 Fig	g5 U3, IEC60598-1
MD7	IEC60950, IE	C61010-1 FigA.2 (2 kohm) for Run function
External MD	Basic measu	ring element 1 kohm
MD Voltage Limit	70 VDC	

DUT POWER		
AC Voltage	0.0 – 277.0 V	
AC Current	40 A max cor	ntinuous
AC Voltage High/Low Limit	Range: Resolution:	0.0 – 277.0 V 0.1 V/step
AC Voltage Display	Range: Resolution: Accuracy:	
Delay Time Setting	Range: Resolution:	
Dwell Time Setting	Range: Resolution: Accuracy:	0.1 sec
Failure Protection		– Neutral Voltage Check (Neutral – V) and ground current check (Line – OC)
GENERAL SPECIF	ICATIONS	
Memory		s, 30 steps per each memory s can link 900 steps max
Mechanical	Bench or rac	kmount with tilt-up feet
Interface	Standard: US Optional: Eth	
Dimensions (W x H x D)	16.93" x 5.24	" x 11.81" (430 x 133 x 300 mm)
Weight	26.45 lbs (12	kg)

Why We Use Counts Associated Research publishes some specifications using "counts" which allows us to provide a better indication of the instrument's capabilities across measurement ranges. A count refers to the lowest resolution of the display for a given measurement range. For example, if the resolution for voltage is 1V then 2 counts = 2 V.

Specifications subject to change without notice.

MedTEST

A Complete Electrical Safety Testing System that Satisfies the Most Demanding Medical **Compliance Requirements**

Our MedTEST system can be designed to provide a complete test solution for medical device manufacturers in need of conforming to IEC 60601-1 3rd Edition Standard. Customize your MedTEST system to satisfy your individual testing requirements including Hipot, Ground Bond, Insulation Resistance, Functional Run and leakage current testing for all B, BF and CF type applied parts including Mains on Applied Parts (MOAP) tests. Up to 40 A of continuous DUT current combined with our Active Link[®] technology reduces overall test time and integration with our SC6540 modular multiplexer allows for multi-point sequential testing without the need to change test leads. Get the most from your test system by utilizing our Autoware®3 software for maximum productivity-enhancing benefits.



AVAILABLE INTERFACES



SAFETY & PRODUCTIVITY FEATURES

Interlock

HV output

Active Link®

Continuous

power during

test steps





Remote Safety SmartGFI Automatic operator shock Easily disable protection

Prompt & Hold Provides alerts & instructions between tests





Multiple Languages Multi-Language user interface

My Menu Customize vour own shortcut menu











DualCHEK® Simultaneous Hipot and Ground Bond

Internal Multiplexer Available with optional HV multiplexer

Modular Multiplexer Compatible with SC6540 multiplexers





Ramp-HI[®]

Hipot

FailCHEK[™] Confirms failure detection

Cal-Alert[®] Tracks and Reduce ramp alerts for time during DC calibration



Accredited Cal





Ground Continuity











•

Charge-LO® Confirms proper DUT

connection Software

Autoware®3 Advanced Automation Control

Accredited calibration options available

AC Hipot

POPULAR MEDTEST CONFIGURATIONS



OMNIA® II 8207 AND SC6540

- All-in-one testing system (Hipot, Ground Bond, Insulation Resistance, and Leakage Current)
- Built in 500 VA AC power source
- Efficient use of rack space
- SC6540 provides automated multi-point testing Most common applications incorporate 8 or 16 port multiplexers



OMNIA® II 8206, SC6540 AND POWERED BY AN (P) AC POWER SOURCE

- All-in-one testing system (Hipot, Ground Bond, Insulation Resistance, and Leakage Current)
- Compatible APT power source provides power to DUT* Available power ratings: 500 VA – 4 kVA
- SC6540 provides automated multi-point testing. Most common applications incorporate 8 or 16 port multiplexers *Choose from APT 8500 Series.



OMNIA® II 8204, 620L, SC6540 AND POWERED BY AN POWER SOURCE

- All-in-one testing system (Hipot, Ground Bond, Insulation Resistance, and Leakage Current)
- Compatible APT power source provides power to DUT* Available power ratings: 500 VA – 4 kVA
- SC6540 provides automated multi-point testing Most common applications incorporate 8 or 16 port multiplexers
- Up to 40 A continuous current capability for applications that draw greater than 16 A of current *Choose from APT 8500 Series.

MedTEST

LINE CONDITION	IS		DIELECTRIC WITH	HSTAND TEST	MODE	
Reverse Power Switch	Switch for po	ower polarity reversal	Output Rating*	5 kV @ 50 mAA 6 kV @ 20 mAE		
Neutral Switch	Neutral swite	ch on/off selection for single fault	Voltage Setting	Range:	0 – 5,000 VAC, 0	– 6,000 VDC
Ground Switch	Ground swit	ch on/off selection for class I single fault		Resolution: Accuracy:	1 V ± (2% of setting	+ 5 V)
PROBE SETTING	S		HI and LO-Limit	AC Total	Range:	0.000-9.999 mA
Surface to Surface	(PH – PL)				Resolution: Accuracy:	0.001 mA ± (2% of setting + 2 counts)
Surface to Line	(PH – L)				Range:	10.00 – 50.00 mA
Ground to Line	(G – L)				Resolution: Accuracy:	0.01 mA ± (2% of Setting + 2 counts)
LEAKAGE LIMIT	SETTINGS			AC Real	Range:	
Touch Current High/Low Limit	Range: Resolution:	0.0 μA – 999.9 μA / 1,000 μA – 9,999 μA / 10.00 mA – 20.00 mA 0.1 μA / 1 μA / 0.01 mA			Resolution: Accuracy:	± (3% of setting + 50 μA)
rms) Touch Current High/Low Limit	Range: Resolution:	0.0 μΑ -999.9 μΑ / 1,000 υΑ – 9,999 μΑ / 10.00 mA – 30.00 mA 0.1 μΑ / 1 μΑ / 0.01 mA			Range: Resolution: Accuracy:	10.00 – 50.00 mA 0.01 mA ± (3% of setting + 50 μA)
(Peak) MEASURING DEV	/ICE MODU	LE		DC	Range: Resolution: Accuracy:	
MD1	UL544NP, UI	_484 , UL923, UL471, UL867, UL697			Range:	-
MD2	UL544P				Resolution: Accuracy:	1 μA ± (2% of setting + 2 counts)
MD3	IEC 60601-1		Ramp HI	> 20 mA peak	maximum, ON/O	
MD4	UL1563		Charge LO	Range:	0.000 – 350.0 μA	A or Auto Set
MD5	IEC60990 Fig IEC61010	g4 U2, IEC60950-1, IEC60335-1, IEC60598-1,IEC60065,	DC Output Ripple	≤ 4% Ripple rn		mA, Resistive Load
MD6	IEC60990 Fig	g5 U3, IEC60598-1	Discharge Timer			sec for capacitor load
ND7	IEC60950, IE	C61010-1 FigA.2 (2 kohm) for Run function			e values in MAX l	
External MD	Basic measu	ring element 1 kohm	Maximum Capacitive Load	1 μF < 1 kV 0.75 μF < 2 kV		iF < 4 kV iF < 6 kV
MD Voltage Limit	70 VDC			0.50 µF < 3 kV		
DUT POWER			Output Frequency	50/60 Hz ± 0.1	% , User Selection	, 400/800 Hz Option
AC Voltage	0.0 – 277.0 V		AC Output Waveform	Sine Wave, Cre	est Factor = 1.3 –	1.5
AC Current	40 A max co		Output Regulation	± (1% of outpu	it + 5 V) from no lo	oad to full load and over input
AC Voltage High/Low Limit	Range: Resolution:	0.0 – 277.0 V 0.1 V/step	Dwell Timer	voltage range	9.9 sec (0=Continu	
AC Voltage Display	Range: Resolution: Accuracy:	0.0 - 277.0 V 0.1 V/step ± (1.5% of reading + 2 counts), 30.0 - 277.0 V	Ramp Timer	DC 0, 0.3 – 999 Ramp-Up AC:	9.9 sec (0=Continu 0.1 – 999.9	
Delay Time Setting	Range: Resolution:	0.5 – 999.9 sec 0.1 sec		Ramp-Down A Ramp-Up DC: Ramp-Down D		
Dwell Time Setting	Range: Resolution: Accuracy:	0, 0.5 – 999.9 sec (0=Continuous) 0.1 sec ± (0.1% of reading + 0.05 seconds)	Ground Continuity	Max. Ground F	.1 A ± 0.01 A, fixe Resistance: $1 \Omega \pm$	
Failure Protection	On Start-Up	– Neutral Voltage Check (Neutral – V) t and ground current check (Line – OC)	Ground Fault Interrupt		nt: 5.0 mA max Speed: < 1 ms	

*Output voltage limited to 3.5 kV with 620L option 03

CONTINUITY TES	T MODE	
Output Current	DC 0.1 A ± 0.0	0001 A
Resistance Display	Range:	0.00 – 10,000.00 Ω
HI and LO-Limit	0.00 - 10,000	2
Dwell Timer	Range:	0.0, 0.3 – 999.9 sec (0=Continuous)
Milliohm Offset	Range:	0.00 – 10.00 Ω
GROUND BOND	TEST MODE	
Output Voltage	Range:	3.00 – 8.00 VAC
Output Frequency	50/60 Hz ± 0.1	%, User Selection
Output Current	Range: Resolution: Accuracy:	1.00 – 40.00 A 0.01 A ± (2 % of setting + 2 counts)
Output Regulation	± (1% of output voltage range	t + 0.02 A) Within maximum load limits, and over input
Maximum Loading	1.00 – 10.00 A 10.01 – 30.00 A 30.01 – 40.00 A	A, 0 – 200 mΩ
HI and LO-Limit	Range:	0 – 150 for 30.01 – 40.00 A
	Range:	0 – 200 for 10.01 – 30.00 A
	Range:	0 – 600 for 6.00 – 10.00 A
	Range:	0 – 600 for 5.99 – 1.00 A
	Resolution:	1 mΩ
	Accuracy:	6.00 – 40.00 A, ± (2% of setting + 2 Counts) 1.00 – 5.99 A, ± (3% of setting + 3 Counts)
Milliohm Offset	Range:	0 – 200 mΩ
INSULATION RES	ISTANCE TES	T MODE
Output Voltage	Range:	30 – 1,000 VDC
Charging Current	Maximum > 20) mA peak
HI and LO-Limit	Range: Resolution:	0.05-99.99 ΜΩ 0.01 ΜΩ
	Range: Resolution:	100.0 – 999.9 ΜΩ 0.1 ΜΩ
	Range: Resolution:	1000 – 50,000 ΜΩ 1 ΜΩ
Charge-LO	0.000 - 3.500	uA or Auto Set
Ramp Timer	Ramp Up: Ramp Down:	0.1 – 999.9 secs 0.0, 1.0 – 999.9 secs
Dwell Timer	0, 0.5 – 999.9 (0=Continuous)
Delay Timer	0.5 – 999.9 sec	S
Ground Fault Interrupt		nt: 5.0 mA max Speed: < 1 ms

GENERAL SPECIF	ICATIONS
Interface	Standard: USB, RS-232 Optional: Ethernet, GPIB
Safety	Built-in SmartGFI® circuit
Memory	620L: 50 memories, 30 steps per memory OMNIA® II: 10,000 steps
AC POWER SOUR	CE
AC Power Source	Up-to 4 kVA compatible power sources available
Configuration	AC Power Source configuration depends on application. MedTEST hardware is configured for testing products with one side of the supply mains at earth potential (Fig 10 UL60601-1). MedTEST hardware is configured for unbalanced 0-277 V DUT input power. Custom Configurations available. Contact us for details.

Why We Use Counts Associated Research publishes some specifications using "counts" which allows us to provide a better indication of the instrument's capabilities across measurement ranges. A count refers to the lowest resolution of the display for a given measurement range. For example, if the resolution for voltage is 1V then 2 counts = 2 V.

Specifications subject to change without notice.



Interconnect our Hypot[®] Series Hipot Instrument with our HYAMP[®] Series Ground Bond instrument to form a complete safety compliance system. Easily operate both instruments from a single point of control on the production line or in a rack. All test systems are safety agency listed, include interconnect cables, and detailed directions on effortlessly interconnecting your system.

	Hypot [®] 3805	Hypot [®] 3865	Hypot [®] 3870
	AC Hipot	AC DC Hipot	AC DC Insulation Hipot Hipot Resistance
HYAMP [®] 3240			
404	System 32-05	System 32-65	System 32-70
Ground Bond			



Applications Consulting provides customized training tailored to your specific company needs.

OUR CONSULTING PACKAGES

Digital Packages

A web-based learning program. Choose from 2 packages; our Consulting on Demand or Customized Digital Package.

On-site Training Package

1-4 day on-site, hands-on training for your production line or R&D lab.

On-site Validation Package

2 or 4 day on-site training to completely satisfy your organization's validation needs.

Visit **ikonixusa.com/consulting** to learn how we can help your team WE WILL HELP MAKE SURE YOUR SYSTEM IS SAFE AND EFFECTIVE



Boost Productivity with our Automation & Data Capturing Software

Compatible with OMNIA® II, HypotULTRA®, LINECHEK® II & SC6540

Discover the benefits of Autoware®3 by taking it for a test drive with our FREE 30 DAY TRIAL Visit arisafety.com/autoware3 to download today!

1 N		1	000
		S. Comment	(Armonie)
182	AND		de Regime Miller
	acti atta	-	a second
			Annal State
and the second se			Constanting out
	all and and a	-	Party Vila Commission and
	-	- 17	Paulo Inciden
0.00	an Bhra		Territorian .

Barcode Capability

Increase production throughput by incorporating a barcode scan. Autoware®3 fully supports direct barcode connection which enables the user to scan model and serial numbers that can be recorded in a data file.

totage IN 12 D-W	Ranging Taxes (cd)	State of the	
HI - Linet Tubel (sell)	Deal Term (a)		
(d - Louis Tubur (sult)	Ramp Deven Term (b)		
All - Land Read (seal)	an beau		
10 - Louis Head (pub) /2 0.000	1 10	Cherrolan	
earcart must man	- ine	Betch Deed Time (
	DEDOUG	-	

BatchTEST®

Shave minutes off your test routines by testing multiple DUT's simultaneously. Combined with a multiplexer, our BatchTEST® feature performs AC/ DC Hipot, Continuity and Insulation Resistance tests on a batch of DUT'S in a convenient 1-step test.

FEATURES AND BENEFITS

Comprehensive Data Capture Improve tractability and customize test results from multiple workstations anywhere on your network. DualCHEK[®] Print Report Functionality Print Report will show both Ground Bond and ACW/DCW results when DualCHEK[®] is performed. Source Code Available Customize Autoware® 3 to fit your needs.



Record, track and store your data with our brand new software as a service.

Compatible with Hypot® & HypotULTRA®

- Unlimited Users
- Remote Instrument Connection
- Intuitive User Interface
- Immediate Cloud Storage



The platform's interface introduces an intuitive user experience making it easy to setup, run tests and view your reports.



Cloud storage ensures that your tests and data will never be lost or altered – all information is stored immediately to the cloud for access at any time.

Try it out for yourself with a free 30-day trial withstand.ikonixusa.com/auth/signup/create

ESSENTIAL WORKSTATION ACCESSORIES

Test Verification Box TVB-2

The TVB-2 is a go/no-go daily test verification box designed to ensure that the failure detectors of an Associated Research electrical safety testing instrument are functioning properly. We designed the TVB-2 to verify Hipot, Insulation Resistance, Ground Bond, and Ground Continuity test functionality. If you perform daily verifications on your testing equipment, then the TVB-2 is an ideal solution. An accessory cord is available to customers who prefer to verify their test instrument using an adapter box.

TVB-2 Accessory Cord 39514


Accessory line cord for the TVB-2 allows convenient connection to a standard adapter box.

Leakage Current Verification Box LVB-2

Verify the failure detectors of your Associated Research Leakage Current Test instrument are functioning properly with this go/no-go load box.

Red/Green Signal Tower Light 39560

Gives an indication as to the status of the testing area. A green light indicates the Hipot instrument is not outputting high voltage and the test area is safe. A red light indicates that the Hipot instrument is active and to stay clear of the test area.















Insulation Mat 39539

Dimensions 36" x 36" (914.4 x 914.4mm)



High Voltage Warning Sign 39538



DUT Enclosure Wood Frame with Foam Interior 39067

Protect your operator from electric shock by enclosing your DUT. Our enclosures automatically disable the instrument's output when the enclosure door is opened. Our DUT Enclosures are designed to protect the operator from electric shock during testing. Interface an enclosure with our Remote Safety Interlock feature to automatically disable the instrument's output when the enclosure door is opened.

Outside dimensions (W x D x H): 24" x 19" x 11.5" (610 x 483 x 293 mm) Inside dimensions (W x D x H):20" x 16" x 10" (508 x 407 x 254 mm) 3/4" Walls, 3/4" Flame Retardant Foam, 1/4" Plexiglass cover



Dual Palm Remote Switch DPR-01

Prevent your operator from touching a DUT as their hands must stay on the test switches to continue to run a test.

Remote Test Box w/LED Indicators RTB-02

Helps maintain a safe distance between the operator and test instrument when starting and restarting a test. Compatible with all models except SC36540.



E-Stop ESTOP

Immediately stop the flow of electric current to your instrument when the E-Stop is triggered. The E-Stop provides the safest and fastest way for a rescuer to save an operator from injury.



COMMON SAFETY STANDARD REFERENCE CHART

Standard/	Testing	Dielectric	: Withstand			Ground Bond	l/Continuity		
Harmonized Standard	Туре	Test Voltage	Max I.	Test Time	Test Current	V Limit	Max. R	Test Time	
IEC/UL 60601-1 3rd Edition	Performance	500 – 4000 VAC or 707 – 5656 VDC	No Breakdown	60 s	10-25 A	≤ 6 V	≤ 0.1 Ω	5 s	
Medical Electrical Equipment	Production*	1000 – 3000 VAC		1 or 60 s	10-25 A	≤ 6 V	≤ 0.1 Ω	5 s	
IEC 61730-2 UL 1703	Performance	1000 VAC + 2 x rated V or 2000 VAC + 4 x rated V	50 uA	60 s	2.5 x Max Over Current Protection	≤ 12 V	≤ 0.1 Ω	120 s	
Photovoltaic Modules & Panels	Production	1000 VAC + 2 x rated V or (1000 VDC + 2 x rated V) X 120%	50 uA	1 or 60 s	Continuity				
IEC 60335-1 Household	Performance	500 – 2400 VAC x rated V + 2400 VAC	No Breakdown	60 s	≥ 10 A	≤ 12 V	0.1 – 0.2 Ω	≤ 120 s	
Electrical Appliances	Production	400 – 2500 VAC	5-30 mA	1 s	≥ 10 A	≤ 12 V	0.1 – 0.2 Ω	No time specified	
UL 60335-1 Household	Performance	500V – 2400 VAC x rated V + 2400 VAC	No Breakdown	60 s	40 A	≤ 6.5 V	≤ 0.5 Ω	120 s	
Electrical Appliances	Production	400 – 2500 VAC	5-30 mA	1 s	40 A	≤ 12 V	0.1 – 0.2 Ω	No time specified	
IEC 60598-1 Luminaires	Performance	500 – 4 x rated V + 2000 VAC	No Breakdown	60 s	≥ 10 A	≤ 12 V	≤ 0.5 Ω	60 s	
	Production		No	ot Specified – Resp	ponsibility of Manufacturer				
UL 1598 Luminaires	Performance	ormance 1000 VAC – 1000 VAC x 2 x rated V No	No Breakdown	60 s	30 A	≤ 4 V	≤ 0.1 Ω	120 s	
	Production	1200 VAC		1 s	Continu	iity	≤ 0.1 Ω	Continuity	
IEC/UL 61010-1 & CSA 22.2 No.	Performance	840 – 11940 VAC or 1200 – 7500 VDC	No Breakdown	5 – 60 s	25 or 30 A	≤ 10 V or ≤ 12 V	≤ 0.1 Ω or < 4 V 0.133 Ω	60 or 120 s	
61010-1 Laboratory Control Test & Measurement Equipment	Production				Continuity				
EN 60204-1 Electrical Equipment	Performance	2 x rated V or 1000 VAC	No Breakdown	1 s	0.2 – 10 A	≤ 24 V	Refer to Section 18.2.2	No time specified	
of Machines	Production		No	ot Specified – Resp	onsibility of Manufacturer				
UL 2202 Electric Vehicle Charging	Performance	500 VAC or 1000 VAC + 2 x rated V	No Breakdown	60 s	≤ 60 A	≤ 12 V	Continuity	120 – 240 s	
System Equipment	Production	1000 – 1700 VAC + 3.4 x rated V		60 or 1 s	Continuity				
IEC 61851-1 Electric Vehicle Conductive	Performance	1200 VAC + rated V or DC Equivalent	No Breakdown	60 s	Continuity				
Charging System	Production		No	ot Specified – Resp	onsibility of Manufactu				
UL 45A Portable Electrical Appliances	Performance	1000 VAC + 2 x rated V or DC equivalent	No Breakdown	60 s	Continuity				
	Production	1000 – 3000 VAC		1 s	Continuity				
EN 60950-1 EN 50116	Performance	1000 – 3000 VAC or 1414 – 4242 VDC	No Breakdown	120 s	30 A	≤ 12 V	≤ 0.1 Ω	60 s	
Information Technology Equipment	Production			1 – 4 s	25 A	≤ 12 V	≤ 0.1 Ω	1-4 s	
UL 60950-1 CSA 22.2 No. 60950-	Performance	1000 – 3000 VAC or 1414 – 4242 VDC	No Breakdown	60 s	≤ 40 A	≤ 12 V	≤ 0.1 Ω	60 s	
1 & IEC 62368-1 Audi/Video, Information & Communication Technology Equipment	no, Production on & Cation IV		ro parformina look	1 – 6 s	Continuity				

*As a result of performing risk analysis, many medical device manufacturers are performing leakage tests as part of 100% production line testing.

Standard/	Testing	Suggested Model	Insulation Resistance			Earth Leakage		
Harmonized Standard	Туре	AR Instrument	Min. R	V Limit	Test Time	Max I.	Test Voltage	
IEC/UL 60601-1 3rd Edition	Performance	8206, 8207, 8256, 8257 or MedTEST	N/A		5-10 mA	110% x rated V		
Medical Electrical Equipment	Production*	7804 or 7854		N/A		5-10 mA	110% x rated V	
IEC 61730-2 UL 1703	Performance	3240, 8206, 8207, 8256, 8257 or MedTEST	40-400 M Ω	500 VDC or Max rated V	10 uA – 1 mA	10 uA – 1 mA	Max rated V	
Photovoltaic Modules & Panels	Production	3240, 3870 or 7850		N/A			N/A	
IEC 60335-1 Household	Performance	8256 or 8257	N/A		1.06 x rated V 0.25 – 5.0 uA			
Electrical Appliances	Production	7804	N/A		N/A			
UL 60335-1 Household Electrical Appliances	Performance	8256 or 8257	N/A		1.06 x rated V 0.25 – 5.0 uA			
	Production	7804	N/A		N/A			
IEC 60598-1 Luminaires	Performance	8206, 8207, 8256 or 8257	1-4 Μ Ω	500 VDC	60 s	0.5 – 10 mA	Rated V	
Luminaires	Production	Hypot [®] or 7850		acturer	onsibility of Manuf	Not Specified – Respo		
UL 1598 Luminaires	Performance	7804 or 7854	≥ 2 MΩ	No time 500 VDC ≥ 2 specified		N/A		
	Production	Hypot [®] or 7850		N/A			N/A	
IEC/UL 61010-1 & CSA 22.2 No.	Performance	8256, 8257 or MedTEST		N/A		0.5 mA	< 300 V	
61010-1 Laboratory Control Test & Measurement Equipment	Production	3865 or 7850		N/A			N/A	
EN 60204-1 Electrical Equipment	Performance	7804 or 7854	≥ 1 MΩ	500 V	No time specified		N/A	
of Machines	Production	Hypot [®] or 7850		acturer	onsibility of Manuf	ot Specified – Respo	N	
UL 2202 Electric Vehicle Charging	Performance	8206, 8207, 8256, 8257 or MedTEST	N/A			0.5 – 0.75 mA or 5 mA	Rated V	
System Equipment	Production	Hypot [®] or 7850	N/A			N/A		
IEC 61851-1 Electric Vehicle Conductive	Performance	8206, 8207, 8256, 8257 or MedTEST	60 s 500 V ≥ 1 MΩ or ≥ 7 MΩ		Touch Current Only			
Charging System	Production	Hypot [®] or 7850	sponsibility of Manufacturer			Not Specified – Respo		
UL 45A Portable Electrical Appliances	Performance	8206, 8207, 8256, 8257 or MedTEST	≥ 50 KΩ	500 V	60 s	0.5 – 3.5 mA	< 300 V	
	Production	Hypot [®] or 7850	N/A		N/A			
EN 60950-1 EN 50116	Performance	8206, 8207, 8256, 8257 or MedTEST	60 s 500 V ≥ 2 MΩ		< 300 V 0.25 – 3.5 mA			
Information Technology Equipment	Production	7804 or 7854		N/A			N/A	
UL 60950-1 CSA 22.2 No. 60950-	Performance	8206, 8207, 8256, 8257 or MedTEST	≥ 2 MΩ	500 V	60 s	0.25 – 3.5 mA	< 300 V	
1 & IEC 62368-1 Audi/Video, Information & Communication Technology Equipment	Production	Hypot [®] or 7850		N/A			N/A	



HEADQUARTERS

28105 N. Keith Drive Lake Forest, IL 60045 USA **Telephone** +1-847-367-4077 **Fax** +1-847-367-4080 **Email** info@ikonixusa.com



ASIA/PACIFIC Telephone +60 3 7842 6097 Fax +60 3 7842 6168

CHINA

SUZHOU / SHANGHAI AREA OFFICE Telephone +86-512-68088360 Fax +86-512-68088359



We Have Local Sales Offices Throughout the World

To find your nearest representative visit us at **arisafety.com**